

# TRAINING, EXPERTISE & RENTAL

## TECHNICAL ASSISTANCE - BeBox\*

- Assessment of current situation
- Supervising, mounting / dismounting support
- Optimization of the assembly process
- Support to use new tools
- Assembly method development for specific problems



## TRAINING & E-LEARNING

- At one of our training Centres, at your location or online (e.g. web seminars)
- Standard training / tailor-made training
- For bearing technology (calculation, lubrication, mounting...)



## EXPERTISE

- Bearing calculation
- Bearing overhaul
- Bearing analysis

## RENTAL\*

- HMV (hydraulic nuts) and pumps
- Induction heaters – SmartTemp range



# LUBRICANTS

## UNIVERSAL / UNIVERSAL+

For **multi purpose** application in industry and for automobiles.



## HEAVY DUTY / HEAVY DUTY +

For very **high pressure** application and **heavy loads**, in heavy industry.



## VIB

For parts subjected to **extensive vibrations** or impact.



## HIGH TEMP MP

For long-term lubrication at **low and high temperature** up to +180°C.



## FOOD AL / FOOD

NSF-H1 grease for **food and pharmaceutical** industries.



## FOOD CHAIN OIL

NSF-H1 oil for chains designed for the **food-processing and pharmaceutical industry**.



## CHAIN OIL

Synthetic oil for **high-temperature chains** up to 250°C.



## ULTRA HIGH TEMP

NSF-H1 grease for **extreme temperatures** up to 260°C, and resistant to aggressive agents.




## HIGH SPEED +

Low temperature grease for very **high speeds**.



 Available in bulk

 Available for automatic lubricators

**Example of reference:**  
LUB UNIVERSAL GREASE / B1kg



# LUBRICATION SOLUTIONS

## SINGLE-POINT LUBRICATION - BOOSTER RANGE

**DRIVE** - Powerful & independant from temperature  
6 bar

**20 references / 120 and 250 cm<sup>3</sup>**

**Example of references:**  
LUBER DRIVE KIT 120-UNIVERSAL +  
LUBER DRIVE REFILL 120 UNIVERSAL +



**READY** - Reliable and economical  
ATEX - 5 bar

**13 references / 60 and 125 cm<sup>3</sup>**

**Example of reference:**  
LUBER READY HEAVY DUTY +



**SMART** - Effective and precise  
ATEX - independant from temperature - 6 bar

**12 references / 125 cm<sup>3</sup>**

**Example of references:**  
LUBER SMART 125 HEAVY DUTY+  
LUBER SMART REFILL 125 HEAVY DUTY+



**INSTALLATION KIT** - For booster range  
Standard or heavy duty

**10 references**

**Example of reference:**  
LUBER HDKIT 1P 30mm BEAM CLAMP



## MANUAL GREASE GUN

**Reference:** LUB GREASE GUN SET

## MULTIPOINT LUBRICATION POLIPUMP RANGE

**12-24 VDC power supply / 80 bar / tank capacity 2 L / 12 to 35 outlets**  
**12 references**

**Example of reference:**  
POLIPUMP-2KG-12 PUM-12VDC-IND



# A FULL RANGE OF MAINTENANCE PRODUCTS AND SERVICES

Dedicated to support your bearing experience



Experts & Tools

\*Service available depending on country

## HOT MOUNTING

Induction heaters -  
SmartTEMP range



The perfect tool to heat bearings and pinions safely.



**SmartTEMP S**  
50 kg max



**SmartTEMP M**  
100 kg max



**SmartTEMP L**  
200 kg max



**SmartTEMP XL / XL PIVOT**  
400 kg max



**SmartTEMP XXL**  
800 kg max



**SmartTEMP XXXL**  
1600 kg max

**Example of reference:**  
TOOL SMART TEMP L / induction heater

## HYDRAULIC MOUNTING AND DISMOUNTING



### HYDRAULIC NUTS - HMV range

**84 references** for shaft diameter from **50 mm to 1000 mm**

**Example of reference:**

TOOL HMV10 EBF / Hydraulic nut



### MANUAL HYDRAULIC PUMP KIT

**2 references** 700 bar, 0,3 L and 0,9 L

**Example of reference:**

TOOL PUMP SET 700B-0,3L / pump with acc



### OIL FOR PUMP 700B 1 L

**Reference:**

TOOL HYDRAULIC OIL 1L



### HYDRAULIC PUSH/PULLER - 3-in-1 tool

**Capacity of 8 t** (thrust & internal gripping)  
and **12 t** (extraction)

**Reference:**

TOOL PUSH/PULLER 8/12 Tons



### SELF-CENTERING HYDRAULIC PULLER

**4 references** - 4 t / 12 t / 20 t / 30 t

**Example of reference:**

TOOL SCHP 4T / Self-center hyd puller



### ACCESSORY CASES

**2 references** - For 4 t and 12 t hydraulic pullers

**Example of reference:**

TOOL AS-SCHP 4T / acc set hyd puller



## MECHANICAL DISMOUNTING



### SELF-CENTERING MECHANICAL PULLER

**3 references** - 2 t / 3 t / 5 t

**Example of reference:**

TOOL SCMP 2/3-120 / Self-center mech puller



### DEEP-GROOVE BALL BEARING PULLER KIT

**From 10 to 100 mm** bearing bore diameters

**Reference:**

TOOL BBPS 10-100 / Ball bearing puller set



### MECHANICAL SPINDLE PULLER

Puller-separator kit

**Reference :**

TOOL BPES 10-105 / Back puller extract set



### TRI-SECTION PULLING PLATE

**4 references** of universal tri-section back puller,  
for a capacity from **4 to 30 t**

**Example of reference:**

TOOL BP3S 50-210 / Tri-section back puller



### BORE PULLER KIT WITH INTERNAL GRIPPING

**2 references** - 5 to 44 mm / 45 to 100 mm  
bearing bore diameters

**Example of reference:**

TOOL BP SET 5-44 / Bore Puller Set



## COLD MOUNTING



### COLD MOUNTING CASE

To mount up to 400 bearings, from **10 to 50 mm**  
**bore diameters**

Aluminium sleeves

**Reference :**

TOOL IFT SET 33 / Industry Fitting Tool Set



### MOUNTING PASTE

**2 references** - 60 g / 500 g

To avoid anti-fretting corrosion

**Example of reference:**

LUB MOUNTING PASTE / T60G



### ADJUSTABLE SPANNERS

**10 references** - From **15 to 180 mm** of nut diameters

Pin and hook spanners

**Example of reference:**

TOOL HS 35-50 / Hook Spanner



## SAFETY AND MEASUREMENT

### HEAT-RESISTANT GLOVES

**Reference:** TOOL GLOVE HEAT RESISTANT



### LASER TEMP 301

**Reference:** TOOL LASERTEMP 301 / IR Thermometer



### CALIBRATED FEELER GAUGES

**Example of reference:**

TOOL FEELER GAUGES 150

