




Brand of NTN Group

AGRIHUB

Your season with
complete peace of mind





Successful seasons come from properly prepared soil

The choice of disc harrow hub can make all the difference.

Designed to offer you both efficiency and peace of mind, **AGRIHUB SNR** lets you stay focused on what really matters to you: **the success of your crops.**

Opting for peace of mind is productivity-enhancing

Choose NTN Europe's expertise in design and sealing for reliable equipment and remarkable productivity.

Pollution is blocked from entering

Thanks to a sealed barrier consisting of 8 lips on the exposed side.

Shock-resistant

Thick, robust hub prevents premature failure.

Ready to install and compatible

with a wide range of equipment.




SEALING

To withstand the numerous sources of pollution and prevent it penetrating inside, the **AGRIHUB SNR** is equipped with a complete sealing system consisting of:


A high-performance sealing system

designed and tested to our high standards




8 sealing lips

on the contaminated side



HOUSING

The housing, which is directly exposed to the shocks and stresses of the ground, must provide mechanical strength and seals stability. It consists of:



A forged steel housing

- selected for its resistant properties
- with a thick cross-section to protect the seal against impacts from stones

Zinc coating


Available products

References	Number of fixing holes	Diameter of the fixing holes	D	J	G	B1	B2	B	L1	L2	Disc diameter	Weight (kg)
HUA151-4M12-S01	4	M12x1.25	117	98	M22x1.5	10	60	102	29	26	< 700	2.00
HUA151-5M12-S01	5	M12x1.25	117	98	M22x1.5	10	60	102	29	26	< 700	1.99
HUA151-6M12-S01	6	M12x1.25	117	98	M22x1.5	10	60	102	29	26	< 700	1.98

►Contact us for any other requests.

Equivalences

Number of fixing holes	SNR hub	Equivalent hub
4	HUA151-4M12-S01	SKF BAA-0004 (T100) SKF BAA-0023 (T100) SKF BAA-0044 (T200) PEER AGHU2898X4E-DSCS (T50) NSK AHU 28117A-01 FKL IL50-98/4T-M22 (or IL40) INA F-673270.04.TILL LFD AGRI.HUB 4 FLT PR040/4x98
5	HUA151-5M12-S01	SKF BAA-0012 SKF BAA-0047 PEER AGHU2898X5E-DSCS NSK AHU 28117A-02 FKL IL50-98/5T-M22 (or IL40) INA F-673270.05.TILL PFI PHA0012
6	HUA151-6M12-S01	SKF BAA-0006 PEER AGHU2898X6E-DSCS NSK AHU 28117A-03 FKL IL50-98/6T-M22 (or IL40) INA F-673270.06.TILL



This document is the exclusive property of NTN Europe. Any total or partial reproduction hereof without the prior consent of NTN Europe is strictly prohibited. Legal action may be brought against anyone breaching the terms of this paragraph. NTN Europe shall not be held liable for any errors or omissions that may have crept into this document despite the care taken in drafting it. Due to our policy of continuous research and development, we reserve the right to make changes without notice to all or part of the products and specifications mentioned in this document.

© NTN Europe, international copyright 2024.

NTN Europe - 1 rue des Usines - 74000 Annecy
 RCS ANNECY B 325 821 072 - Code APE 2815Z - Code NACE 28.15
www.ntn-europe.com