
# EXTEND THE LIFE **OF YOUR BEARINGS**



www.ntn-snr.com

With You

# Choose the right grease for your bearings



NTN-SNR simplifies your choice with a range of professional greases.

## **UNIVERSAL** Multi purpose





#### Grease for general use, for automotive and industrial applications

**Advantages:** Good performance in the presence of water, excellent protection against wear and corrosion.

**Typical applications:** Agricultural equipment, washing machines, materials handling equipment, general machinery, low power electric motors, automobile wheel bearings, small tools...

Temperature range: -25 to +140 °C



# HEAVY DUTY High load

Extreme pressure, multi-service grease, designed for intensive applications in heavy industry: steel industry, construction, transport, etc.

**Advantages:** Excellent performance under very high loads, at high and low speed, good performance in the presence of water, excellent protection against wear and corrosion.

Typical applications: High power electric motors, conveyors, lifting equipment, lorry wheel hubs, water pumps, presses...

Temperature range: -25 to +140 °C



Provides perfect lubrication to bearings subject to high levels of vibration or shocks loads. Recommended for quarries, cement plants, civil and agricultural works, and high-load applications in a humid environment: paper mills, excavation, etc.

Advantages: Excellent resistance to shocks, high levels of vibration and heavy loads, excellent water-resistance that guarantees long life.

Typical applications: Bucket spindles, grinders, crushers, vibrating screens, washing machines, industrial fans...

Temperature range: -20°C to +140°C





With You



### **HIGH TEMP MP** High temperature

The ideal solution for long-term lubrication at low and high temperatures up to 180 ° C.

Advantages: Polyurea extreme pressure multi-purpose grease which offers excellent protection against wear and corrosion. Silent, it is perfect for lubricating bearings in electric motors.

Typical applications: Electric motors, dryers, oven conveyors, generators, pumps, textile machines, processing machines paper ...

Wide temperature range: -40 ° C to + 180 ° C





- assists with bearing installation and maintenance: advice on lubrication, provide support for your bearing application, technical training, maintenance audits.
- makes your work simpler and more reliable thanks to a range of specialised tools: extractors, separators, bearing heaters, spanners, hydraulic nuts and pumps, thermometers, etc.

#### For more information about our entire offer, contact NTN-SNR Experts & Tools on our Website www.ntn-snr.com

This document is the exclusive property of NTN-SNR ROULEMENTS. Any total or partial reproduction hereof without the prior consent of NTN-SNR ROULEMENTS is strictly prohibited. Legal action may be brought against anyone breaching the terms of this paragraph. NTN-SNR ROULEMENTS shall not be held liable for any errors or omissions that may have crept into this document despite the care taken in drafting it. Due to our policy of continuous research and development, we reserve the right to make changes without notice to all or part of the products and specifications mentioned in this document. © NTN-SNR ROULEMENTS, International copyright 2018.

NTN-SNR ROULEMENTS - 1 rue des Usines - 74000 Annecy

RCS ANNECY B 325 821 072 - Code APE 2815Z - Code NACE 28.15 www.ntn-snr.com Distributed by

