# DEEP-GROOVE BALL BEARINGS ENJOY THE SILENCE



www.ntn-snr.com



With You



ALL OUR STANDARD 6XXX BEARINGS

THE CM CLEARANCE

## STANDARD DEEP-GROOVE BALL BEARINGS

#### SIMPLICITY ALSO DESERVES THE BEST QUALITY

By listening to those working on the field, we know that quiet running is of the highest importance to our customers. That's why NTN has established the new internal **CM** clearance for all these bearing types:



### 249 PART NUMBERS, MADE BY NTN, FEATURE THE CM CLEARANCE

#### THE RANGE

	SUFFIX			BOI																									
	6000 SERIES	00	01	02	03	04	05	06	07	08	09	10	11	12	13	14	15	16	17	18	19	20	21	22	24	26	28	30	32
Open	60xx <b>CM</b>																												
Shields	60xxZZ <b>CM</b> /5K																												
Contact seals	60xxLLUCM/5K																												
Non-contact seals	60xxLLBCM/5K																												
	6200 SERIES	00	01	02	03	04	05	06	07	08	09	10	11	12	13	14	15	16	17	18	19	20	21	22	24	26	28	30	32
Open	62xxCM																												
Shields	62xxZZ <b>CM</b> /5K																												
Contact seals	62xxLLUCM/5K																												
Non-contact seals	62xxLLBCM/5K																												
	6300 SERIES	00	01	02	03	04	05	06	07	08	09	10	11	12	13	14	15	16	17	18	19	20	21	22	24	26	28	30	32
Open	63xxCM																												
Shields	63xxZZCM/5K																												
Contact seals	63xxLLUCM/5K																												
Non-contact seals	63xxLLBCM/5K																												

Previous designation: 60xxLLU/5K > new designation: 60xxLLUCM/5K



Thanks to narrower **CM** clearance which reduces vibration, **NTN** divides the noise level of bearings by 2.

This sound comfort is guaranteed by 100% quality control.










100% QUALITY CONTROL NOISE LEVEL **REDUCED TO HALF** 





Replacing the **CN** clearance with the **CM** clearance **has no impact on mounting.** 

Both clearances meet the ISO standard and are interchangeable:

- 1 Identical mounting parameters
- No additional approvals
- **3** Unchanged load capacities

#### **CLEARANCES**

BORE CODES FOR SERIES 60, 62 AND 63	NORMAL INTERNAL CN CLEARANCE IN MICRONS	NEW SPECIAL INTERNAL <b>CM</b> CLEARANCE IN MICRONS
00	2 to 13	4 to 11
from 01 to 03 included	3 to 18	4 to 11
from 04 to 06 included	5 to 20	5 to 12
from 07 to 08 included	6 to 20	9 to 17
from 09 to 10 included	6 to 23	9 to 17
from 11 to 13 included	8 to 28	12 to 22
from 14 to 16 included	10 to 30	12 to 22
from 17 to 20 included	12 to 36	18 to 30
from 21 to 24 included	15 to 41	18 to 30
from 26 to 28 included	18 to 48	24 to 38
from 30 to 32 included	18 to 53	24 to 38



# **ENJOY THE SILENCE**

This document is the exclusive property of NTN-SNR ROULEMENTS. Any total or partial reproduction hereof without the prior consent of NTN-SNR ROULEMENTS is strictly prohibited. Legal action may be brought against anyone breaching the terms of this paragraph. NTN-SNR ROULEMENTS shall not be held liable for any errors or omissions that may have crept into this document despite the care taken in drafting it. Due to our policy of continuous research and development, we reserve the right to make changes without notice to all or part of the products and specifications mentioned in this document.

© NTN-SNR ROULEMENTS, international copyright 2019.

