



Brand of NTN Group

AGRIHUB

Your season with
complete peace of mind



AGRIHUB
INSTALL IT, RUN IT, FORGET IT.



Successful seasons come from properly prepared soil

The choice of disc harrow hub can make all the difference.


Designed to offer you both efficiency and peace of mind, **AGRIHUB SNR** lets you stay focused on what really matters to you: **he success of your crops.**

SEALING

To withstand the numerous sources of pollution and prevent it penetrating inside, the **AGRIHUB SNR** is equipped with a complete sealing system consisting of:

A high-performance sealing system
designed and tested to our high standards

8 sealing lips
on the contaminated side




HOUSING

The housing, which is directly exposed to the shocks and stresses of the ground, must provide mechanical strength and seals stability. It consists of:

A forged steel housing

- selected for its resistant properties
- with a thick cross-section to protect the seal against impacts from stones

Zinc coating



INSTALL IT, RUN IT, FORGET IT.

AGRIHUB

Opting for peace of mind is productivity-enhancing

Choose NTN Europe's expertise in design and sealing for reliable equipment and remarkable productivity.



Pollution is blocked from entering

Thanks to a sealed barrier consisting of 8 lips on the exposed side.

Shock-resistant

Eviter les défaillances prématurées grâce à un moyeu épais et robuste.

Ready to install and compatible

with a wide range of equipment.


Available products

References	Number of fixing holes	Diameter of the fixing holes	D	J	G	B1	B2	B	L1	L2	Disc diameter	Weight (kg)
HUA151-4M12-S01	4	M12x1.25	117	98	M22x1.5	10	60	102	29	26	< 700	2.00
HUA151-5M12-S01	5	M12x1.25	117	98	M22x1.5	10	60	102	29	26	< 700	1.99
HUA151-6M12-S01	6	M12x1.25	117	98	M22x1.5	10	60	102	29	26	< 700	1.98

►Contact us for any other requests.

Equivalences

Number of fixing holes	SNR hub	Equivalent hub
4	HUA151-4M12-S01	SKF BAA-0004 (T100) SKF BAA-0023 (T100) SKF BAA-0044 (T200) PEER AGHU2898X4E-DSCS (T50) NSK AHU 28117A-01 FKL IL50-98/4T-M22 (or IL40) INA F-673270.04.TILL LFD AGRI.HUB 4 FLT PR040/4x98
5	HUA151-5M12-S01	SKF BAA-0012 SKF BAA-0047 PEER AGHU2898X5E-DSCS NSK AHU 28117A-02 FKL IL50-98/5T-M22 (or IL40) INA F-673270.05.TILL PFI PHA0012
6	HUA151-6M12-S01	SKF BAA-0006 PEER AGHU2898X6E-DSCS NSK AHU 28117A-03 FKL IL50-98/6T-M22 (or IL40) INA F-673270.06.TILL



Ten dokument jest wyłączną własnością NTN Europe. Wszelkie całkowite lub częściowe powielanie niniejszej publikacji, bez uprzedniej zgody NTN Europe jest surowo zabronione. Działania prawne mogą być wytoczone przeciwko każdemu naruszeniu warunków niniejszej informacji. NTN Europe nie ponosi odpowiedzialności za ewentualne błędy lub braki, które mogą pojawić się w niniejszym dokumencie, mimo staranności przy jego sporządzaniu. Z uwagi na politykę ciągłych badań i rozwoju, zastrzegamy sobie prawo do wprowadzania poprawek do całości lub części opisów produktów i specyfikacji wymienionych w tym dokumencie bez uprzedniego powiadomienia.
© NTN Europe, międzynarodowe prawa autorskie 2025.

NTN Europe - 1 rue des Usines - 74000 Annecy
RCS ANNECY B 325 821 072 - Code APE 2815Z - Code NACE 28.15
www.ntn-europe.com