

# BALL BEARING SENSOR INCREMENTAL

The perfect innovation for a better production

FOR MASS PRODUCTION



[www.ntn-snr.com](http://www.ntn-snr.com)



With You



## MEASURE SPEED

### WITH A BALL BEARING INTEGRATION

#### INTEGRATED

- Ball bearing integration
- Hollow-shaft


#### INDUSTRY STANDARD

- Reliable
- Standard bearing



## CONFIGURATION

BBS	TYPE	BALL BEARING						OUTPUT	
	INC							Wire, Connector	
		$\varnothing A$	$\varnothing B$	C	$\varnothing D$	$\varnothing E$	F	ppr	
		6202	15	35	11	18	32	7,5	32
		6204	20	47	14	29,5	46,6	7,5	48
		6206	30	62	16	40,6	58	7,5	64
		6208	40	80	18	53	75	7,5	80
		6209	45	85	19	57,3	77	7,5	80



## SPECIFICATION

- Input Voltage: 5-24V
- Output signal: Open collector (check datasheet for pull-up resistor needed values)
- Operating temperature: -25°C to 120°C
- Power supply frequency and magnetic field standard (EN611000-4-8)

This document is the exclusive property of NTN-SNR ROULEMENTS. Any total or partial reproduction hereof without the prior consent of NTN-SNR ROULEMENTS is strictly prohibited. Legal action may be brought against anyone breaching the terms of this paragraph.

NTN-SNR ROULEMENTS shall not be held liable for any errors or omissions that may have crept into this document despite the care taken in drafting it. Due to our policy of continuous research and development, we reserve the right to make changes without notice to all or part of the products and specifications mentioned in this document.

© NTN-SNR ROULEMENTS, international copyright 2018.

NTN-SNR ROULEMENTS - 1 rue des usines - 74000 Annecy  
RCS ANNECY B 325 821 072 - Code APE 2815Z - Code NACE 28.15  
[www.ntn-snr.com](http://www.ntn-snr.com)

Contact us:

[mechatronics.industry@ntn-snr.fr](mailto:mechatronics.industry@ntn-snr.fr)



With You

