

Product :	LUB VIB	
Code : C32001-NTN	Version : 1.9	Revision : 23-July-2015

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Trade name or designation of the mixture	LUB VIB
Registration number	-
Synonyms	None.
Product code	C32001-NTN

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses	See Technical Data Sheet.
Uses advised against	Not available.

1.3. Details of the supplier of the safety data sheet

Supplier

Company name	NTN-SNR ROULEMENTS	
Address	1, rue des Usines BP 2017 74000 ANNECY FR	

Division

Telephone	Tel.:	+33 (0)4 50 65 30 00
	Fax:	+33 (0)4 50 65 32 91

e-mail	audrey.bornes@ntn-snr.fr
---------------	--------------------------

Contact person	Service Laboratoire NTN-SNR Roulements
-----------------------	--

1.4. Emergency telephone number	Emergency Tel. (Office hours)	+33 (0)4 50 65 97 55
--	-------------------------------	----------------------

Emergency Tel. (France)	ORFILA (INRS)	+ 33 (0)1 45 42 59 59
-------------------------	---------------	-----------------------

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

The mixture has been assessed and/or tested for its physical, health and environmental hazards and the following classification applies.

Classification according to Directive 67/548/EEC or 1999/45/EC as amended

This preparation does not meet the criteria for classification according to Directive 1999/45/EC as amended.

Classification according to Regulation (EC) No 1272/2008 as amended

This mixture does not meet the criteria for classification according to Regulation (EC) 1272/2008 as amended.

Hazard summary

Specific hazards	Under normal conditions of intended use: None known.
Main symptoms	See section 11 for additional information on health hazards.

2.2. Label elements

Label according to Regulation (EC) No. 1272/2008 as amended

Hazard pictograms	None.
Signal word	None.
Hazard statements	The mixture does not meet the criteria for classification.

Precautionary statements

Prevention	Observe good industrial hygiene practices.
Response	Wash hands after handling.

Product :	LUB VIB	
Code : C32001-NTN	Version : 1.9	Revision : 23-July-2015

Storage	Store away from incompatible materials.
Disposal	Not applicable.
Supplemental label information	Contains Benzenesulfonic acid, di-C10-14-alkyl derivs., calcium salts. May produce an allergic reaction.
2.3. Other hazards	Not assigned.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

General information

Chemical name	%	CAS-No. / EC No.	REACH Registration No.	INDEX No.	Notes
Phosphorodithioic acid, mixed O,O-bis(2-ethylhexyl and iso-Bu and iso-Pr) esters, zinc salts	1 - < 3	85940-28-9 288-917-4	-	-	

Classification: **DSD:** Xi;R36-38, N;R51/53
CLP: Skin Irrit. 2;H315, Eye Irrit. 2;H319, Aquatic Chronic 2;H411

CLP: Regulation No. 1272/2008. "-" = Not available or this substance does not meet the criteria for classification according to Regulation (EC) 1272/2008 as amended.
DSD: Directive 67/548/EEC.
M: M-factor
vPvB: very persistent and very bioaccumulative substance.
PBT: persistent, bioaccumulative and toxic substance.
#: This substance has been assigned Community workplace exposure limit(s).

Composition comments Occupational Exposure Limits for constituents are listed in Section 8. The full text for all R- and H-phrases is displayed in section 16.

- Contains : Mineral oil
DMSO Extract < 3% according to IP 346 Method.

SECTION 4: First aid measures

General information Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves.

4.1. Description of first aid measures

Inhalation	Under normal conditions of intended use, this material is not expected to be an inhalation hazard.
Skin contact	Wash off with soap and water. Get medical attention if irritation develops and persists.
Eye contact	Rinse with water. Get medical attention if irritation develops and persists.
Ingestion	Rinse mouth thoroughly. If swallowed, do NOT induce vomiting. Get medical attention if symptoms occur.

4.2. Most important symptoms and effects, both acute and delayed Frequent or prolonged contact may defat and dry the skin, leading to discomfort and dermatitis.

4.3. Indication of any immediate medical attention and special treatment needed Treat symptomatically.

Product :

LUB VIB

Code : C32001-NTN

Version : 1.9

Revision : 23-July-2015

SECTION 5: Firefighting measures

General fire hazards	No unusual fire or explosion hazards noted.
5.1. Extinguishing media	
Suitable extinguishing media	Foam. Dry chemicals. Carbon dioxide (CO ₂). Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.
5.2. Special hazards arising from the substance or mixture	Combustible. See also section 10.
5.3. Advice for firefighters	
Special protective equipment for firefighters	Self-contained breathing apparatus and full protective clothing must be worn in case of fire.
Special fire fighting procedures	In case of fire and/or explosion do not breathe fumes. Cool containers exposed to heat with water spray and remove container, if no risk is involved.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures	
For non-emergency personnel	Keep unnecessary personnel away. Wear appropriate protective equipment and clothing during clean-up. For personal protection, see section 8.
For emergency responders	Keep unnecessary personnel away. Use personal protection recommended in Section 8 of the MSDS.
6.2. Environmental precautions	Local authorities should be advised if significant spillages cannot be contained. Avoid discharge into drains, water courses or onto the ground.
6.3. Methods and material for containment and cleaning up	The product is immiscible with water and will spread on the water surface. Stop the flow of material, if this is without risk.
6.4. Reference to other sections	See Section 8 for personal protective equipment. For waste disposal, see section 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling	To avoid thermal decomposition, do not overheat. Avoid prolonged or repeated contact with skin. Wash hands after handling. Handle in accordance with good industrial hygiene and safety practices. Adequate ventilation should be provided so that exposure limits are not exceeded.
7.2. Conditions for safe storage, including any incompatibilities	Keep away from heat and sources of ignition. Store in closed original container in a dry place. Store away from incompatible materials (see Section 10 of the MSDS).
7.3. Specific end use(s)	Not available.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters	
Occupational exposure limits	No exposure limits noted for ingredient(s).
Biological limit values	No biological exposure limits noted for the ingredient(s).
Recommended monitoring procedures	Follow standard monitoring procedures.
Derived no-effect level (DNEL)	Not available.
Predicted no effect concentrations (PNECs)	Not available.

Product :

LUB VIB

Code : C32001-NTN

Version : 1.9

Revision : 23-July-2015

Exposure guidelines Occupational Exposure Limits are not relevant to the current physical form of the product.

8.2. Exposure controls

Appropriate engineering controls Ensure adequate ventilation, especially in confined areas.

Individual protection measures, such as personal protective equipment

General information Personal protection equipment should be chosen according to the CEN standards and in discussion with the supplier of the personal protective equipment.

Eye/face protection Chemical goggles are recommended.

Skin protection

- **Hand protection** Use protective gloves made of: Nitrile. Polyvinyl chloride (PVC).

- **Other** Normal work clothing (long sleeved shirts and long pants) is recommended.

Respiratory protection In case of insufficient ventilation, wear suitable respiratory equipment.

Thermal hazards Wear appropriate thermal protective clothing, when necessary.

Hygiene measures Wash hands after handling. Handle in accordance with good industrial hygiene and safety practices.

Environmental exposure controls Environmental manager must be informed of all major releases.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance

Physical state Solid.

Form Solid. Paste.

Colour Blonde.

Odour Mild.

Odour threshold Not available.

pH Not applicable.

Melting point/freezing point Not available.

Initial boiling point and boiling range Not available.

Flash point > 200.0 °C (> 392.0 °F) Cleveland open cup Base oil

Evaporation rate Not available.

Upper/lower flammability or explosive limits

Flammability limit - lower (%) Not available.

Flammability limit - upper (%) Not available.

Vapour pressure Not available.

Vapour density Not available.

Relative density 0.9

Relative density temperature 20 °C (68 °F)

Solubility(ies) Insoluble

Partition coefficient (n-octanol/water) Not available.

Auto-ignition temperature > 250 °C (> 482 °F)

Product :

LUB VIB

Code : C32001-NTN

Version : 1.9

Revision : 23-July-2015

Decomposition temperature	Not available.
Viscosity	Not applicable.
Viscosity temperature	40 °C (104 °F)
Explosive properties	Not available.
Oxidizing properties	Not available.
9.2. Other information	
Drop point	190 °C (374 °F)
Kinematic viscosity	Not applicable.
Kinematic viscosity temperature	40 °C (104 °F)

SECTION 10: Stability and reactivity

10.2. Chemical stability	Material is stable under normal conditions.
10.3. Possibility of hazardous reactions	No dangerous reaction known under conditions of normal use.
10.4. Conditions to avoid	Avoid temperatures exceeding the decomposition temperature. Avoid temperatures exceeding the flash point. Eliminate all sources of ignition. Contact with incompatible materials.
10.5. Incompatible materials	Strong oxidising agents.
10.6. Hazardous decomposition products	Carbon oxides.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity	Elevated temperatures or mechanical action may form vapours, mist, or fumes which may be irritating to the eyes, nose, throat, or lungs. Ingestion of large amounts may produce gastrointestinal disturbances including irritation, nausea, and diarrhoea.
Skin corrosion/irritation	Frequent or prolonged contact may defat and dry the skin, leading to discomfort and dermatitis.
Serious eye damage/eye irritation	Not classified.
Respiratory sensitisation	Not classified.
Skin sensitisation	Not classified.
Germ cell mutagenicity	Not classified.
Carcinogenicity	Not classified.
Reproductive toxicity	Not classified.
Specific target organ toxicity - single exposure	Not classified.
Specific target organ toxicity - repeated exposure	Not classified.
Aspiration hazard	Not classified.
Mixture versus substance information	No information available.
Other information	Not available.

SECTION 12: Ecological information

12.1. Toxicity	Not classified as an environmental hazard.
-----------------------	--

Product :

LUB VIB

Code : C32001-NTN

Version : 1.9

Revision : 23-July-2015

12.2. Persistence and degradability	No data is available on the degradability of this product.
12.3. Bioaccumulative potential	No data available.
Partition coefficient n-octanol/water (log Kow)	Not available.
Bioconcentration factor (BCF)	Not available.
12.4. Mobility in soil	No data available.
Mobility in general	The product is immiscible with water and will spread on the water surface.
12.5. Results of PBT and vPvB assessment	Not available.
12.6. Other adverse effects	No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Residual waste	Dispose of in accordance with local regulations. Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe manner (see: Disposal instructions).
Contaminated packaging	Empty containers should be taken to an approved waste handling site for recycling or disposal. Since emptied containers may retain product residue, follow label warnings even after container is emptied.
EU waste code	Unused product : 16 03 06 Waste codes should be assigned by the user based on the application for which the product was used.
Disposal methods/information	Collect and reclaim or dispose in sealed containers at licensed waste disposal site. Do not discharge into drains, water courses or onto the ground.
Special precautions	Dispose in accordance with all applicable regulations.

SECTION 14: Transport information

ADR

Not regulated as dangerous goods.

IATA

Not regulated as dangerous goods.

IMDG

Not regulated as dangerous goods.

14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code This substance/mixture is not intended to be transported in bulk.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

EU regulations

Regulation (EC) No. 1005/2009 on substances that deplete the ozone layer, Annex I

Not listed.

Regulation (EC) No. 1005/2009 on substances that deplete the ozone layer, Annex II

Not listed.

Product :

LUB VIB

Code : C32001-NTN

Version : 1.9

Revision : 23-July-2015

Regulation (EC) No. 850/2004 On persistent organic pollutants, Annex I as amended

Not listed.

Regulation (EC) No. 689/2008 concerning the export and import of dangerous chemicals, Annex I, part 1 as amended

Not listed.

Regulation (EC) No. 689/2008 concerning the export and import of dangerous chemicals, Annex I, part 2 as amended

Not listed.

Regulation (EC) No. 689/2008 concerning the export and import of dangerous chemicals, Annex I, part 3 as amended

Not listed.

Regulation (EC) No. 689/2008 concerning the export and import of dangerous chemicals, Annex V as amended

Not listed.

Regulation (EC) No. 166/2006 Annex II Pollutant Release and Transfer Registry

Not listed.

Regulation (EC) No. 1907/2006, REACH Article 59(1) Candidate List as currently published by ECHA

Not listed.

Authorisations

Regulation (EC) No. 1907/2006, REACH Annex XIV Substances subject to authorization, as amended

Not listed.

Restrictions on use

Regulation (EC) No. 1907/2006, REACH Annex XVII Substances subject to restriction on marketing and use as amended

Not listed.

Directive 2004/37/EC: on the protection of workers from the risks related to exposure to carcinogens and mutagens at work

Not listed.

Directive 92/85/EEC: on the safety and health of pregnant workers and workers who have recently given birth or are breastfeeding

Not listed.

Other EU regulations

Directive 96/82/EC (Seveso II) on the control of major-accident hazards involving dangerous substances

Not listed.

Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work

Not listed.

Directive 94/33/EC on the protection of young people at work

Not listed.

Other regulations

The product is classified and labelled in accordance with EC directives or respective national laws. This Safety Data Sheet complies with the requirements of Regulation (EC) No 1907/2006.

National regulations

Follow national regulation for work with chemical agents.

15.2. Chemical safety assessment

No Chemical Safety Assessment has been carried out.

SECTION 16: Other information

List of abbreviations

Not available.

References

Not available.

Information on evaluation method leading to the classification of mixture

The classification for health and environmental hazards is derived by a combination of calculator methods and test data, if available.

Product :

LUB VIB

Code : C32001-NTN

Version : 1.9

Revision : 23-July-2015

Full text of any statements or R-phrases and H-statements under Sections 2 to 15

R36 Irritating to eyes.

R38 Irritating to skin.

R51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

H315 Causes skin irritation.

H319 Causes serious eye irritation.

H411 Toxic to aquatic life with long lasting effects.

Revision information

None.

Training information

Follow training instructions when handling this material.