

# EXTEND THE LIFE OF YOUR BEARINGS

## CHOOSE THE RIGHT GREASE FOR YOUR BEARINGS:

NTN-SNR SIMPLIFIES YOUR CHOICE WITH A RANGE OF PROFESSIONAL GREASES



### UNIVERSAL Multi purpose

Your application conforms to conditions of general use. Your bearings work under normal loads.




### HEAVY DUTY High load

Your application can cause high stresses in the bearing. Your bearings work under very high loads.



### VIB Vibrations & shocks

Your application generates a high level of shock load or vibration. Your bearings are subjected to high accelerations.



### HIGH TEMP High temperature

Your application is a hot environment. Your bearings operate continually above 130°C.

## UNIVERSAL Multi purpose



**Grease for general use, for automotive and industrial applications**

**Advantages :** Good performance in the presence of water, excellent protection against wear and corrosion.

**Typical applications :** Agricultural equipment, washing machines, materials handling equipment, general machinery, low power electric motors, automobile wheel bearings, small tools...

**Temperature range :** -25 to +140 °C



## HEAVY DUTY High load



**Extreme pressure, multi-service grease, designed for intensive applications in heavy industry: steel industry, construction, transport, etc.**

**Advantages :** Excellent performance under very high loads, at high and low speed, good performance in the presence of water, excellent protection against wear and corrosion.

**Typical applications :** High power electric motors, conveyors, lifting equipment, lorry wheel hubs, water pumps, presses...

**Temperature range :** -25 to +140 °C



## VIB Vibrations & shocks



**Provides perfect lubrication to bearings subject to high levels of vibration or shocks loads. Recommended for quarries, cement plants, civil and agricultural works, and high-load applications in a humid environment: paper mills, excavation, etc.**

**Advantages:** Excellent resistance to shocks, high levels of vibration and heavy loads, excellent water-resistance that guarantees long life.

**Typical applications:** Bucket spindles, grinders, crushers, vibrating screens, washing machines, industrial fans...

**Temperature range:** -20°C to +140°C



## HIGH TEMP High temperature

**The ideal solution for long-life, high-temperature lubrication up to +150°C. Accepts occasional peaks up to +175°C**

**Advantages:** Extreme long-term, high temperature performance, excellent protection against wear and corrosion, suitable for ball or roller bearings, suitable for horizontal and vertical axes.

**Typical applications:** Textile machines, paper converting machinery, heater, dryer fans, tension pulleys, automobile water pumps...

**Wide temperature range:** -40°C to +160°C



## Experts & Tools With You

- assists with bearing installation and maintenance: advice on lubrication, provide support for your bearing application, technical training, maintenance audits.
- makes your work simpler and more reliable thanks to a range of specialised tools: extractors, separators, bearing heaters, spanners, hydraulic nuts and pumps, thermometers, etc.

**For more information**  
about our entire offer, contact  
NTN-SNR Experts & Tools on our Website  
[www.nten-snr.com](http://www.nten-snr.com)

Distributed by



[www.nten-snr.com](http://www.nten-snr.com)