


Unique with its back & forth design

3 good reasons to use the hydraulic nuts from NTN SNR

- The most professional tool to provide the drive up force required
- Precise and reliable adjustment of radial bearing clearance
- Cost effective, easy to use and secure, it will reduce your down time



HMV technical data



Distributed by:

strictly prohibited. Legal action may be brought against anyone breaching the terms of this parag /ENTS shall not be held liable for any errors or omissions that may have crept into this document despite tice to all or part of the products and specifications menti © NTN-SNR ROULEMENTS, international copyright 202

NTN-SNR ROULEMENTS - 1 rue des Usines - 74000 Annecy RCS ANNECY B 325 821 072 - Code APE 2815Z - Code NACE 28.15 www.ntn-snr.com




NTN. SNR. NTN-SNR HYDRAULIC NUTS **A MUST FOR MOUNTING /** DISMOUNTING www.ntn-snr.com


your spherical roller bearings with tapered bore

With You

Assemble or disassemble your spherical roller bearings with HMV in only 3 steps.



SELECT THE RIGHT **HMV** Using the selection tables available on request (overview here below)



			HMV HYDRAULI	C NUTS WITH ADAP	PTER SLEEVE		
Shaft diametre (mm)	Bearing bore (mm)		SRB	Adapter Sleeve	HMV used for mounting + dismounting	Locknuts	Washer
45 50	50	21310VK	22210 EK	H310		KM10	MB10
	50	22310EK		H2310		KM10	MB10
50 55	55	21311VK	22211 EK	H311		KM11	MB11
	55	22311EK		H2311		KM11	MB11
	<u> </u>	21312VK	22212 EK	H312	HMV12 FRF	KM12	MB12
55 60	00	22312EK	ļ	H2312		KM12	MB12
		239/950 VK	i i	H39/950H	HMV190 EBF		İ
900	950	230/950 EK		H30/950H			
		240/950EK30		H240/950H			
950	1000	230/1000 EK		H30/1000H	HMV200 EBF		
		240/1000EK30		H240/1000			

Technical data concerning the HMV

• HMV nut is supplied with:

- Two hydraulic connection points.
- One quick coupling connection (male) that can be positioned on the front face or on the outside diameter.
- 3 holes in the front face are provided for mounting the dial gauge (not included).
- tommy bar

Max. permitted	HMV 10 EBF to HMV 25 EBF	700 bar
operating pressure at max.	HMV 26 EBF to HMV 40 EBF	550 bar
piston stroke	HMV 41 EBF to HMV 60 EBF	450 bar
	HMV 62 EBF to HMV 100 EBF	400 bar
	HMV 102 EBF to HMV 120 EBF	350 bar
	HMV 126 EBF to HMV 200 EBF	300 bar

- Easy handling with eye bolt for nut sizes HMV60 EBF and upward
- Tommy bar supplied and the provision of 4 holes on the outer diameter
- HMV's available in metric and inch sizes (1.967 to 37.410 inch)
- Special sizes on request



NUTS	s with wi	THDRAWA	L SLEEVE		
	withdrawl Sleeve	HMV used for mounting	HMV used for mounting + dismounting	Locknuts	Washer
	AH 313	HMV12 EBF	HMV15 EBF		
	AH313G		HMV14 EBF	KM12	MB12
	AH 2313		HMV15 EBF		
	AH2313G		HMV14 EBF	KM12	MB12
	AH314		HMV16 EBF		
	AH314G	HMV13 EBF	HMV15 EBF	KM13	MB13
	AHX2314	HIVIV I 3 EBF	HMV16 EBF		
	AHX2314G]	HMV15 EBF	KM13	MB13
	AH 2314		HMV17 EBF		
	A0H39/950		HMV200 EBF		
	AH30/950		HMV200 EBF		
	A0H30/950	HMV180 EBF	HMV200 EBF	HM30/900	MS30/900
	A0H240/950	1	HMV200 EBF	HM30/900	MS30/900

Accessories for HMV:

- Dial gauge: 2 sizes available (050 & 100) in order to measure the displacement from 5mm to 10mm
- Adapter kit for dial gauge: 4 sizes included with the kit




With You



a Screw the HMV on the thread until the bearing and HMV are in contact. Warning : Do not forget to grease the thread!

b Connect the pump to the HMV.



C Mount the dial gauge (not included) onto the HMV using the dial gauge holder (supplied with the HMV). Set the gauge to " 0 ".



Pump used with HMV


- 3 kits designed to provide the best service to your HMV
- Tool pumps set 700 b 0.3 L for nuts <= HMV 54 EBF
- Tool pumps set 700 b 0.9 L for nuts <= HMV 92 EBF
- Tool pumps set 1500 b 2.5 L for nuts <= HMV 200 EBF

All the kits include:

- pressure gauge - high quality hose (1.5m for the pump 700 b 0.3 L & 3 m
- for the 700b 0.9L and 1500b 2.5L) - 1 guick coupling connection (female)
- supplied with hydraulic oil




d Activate the pump until you reach the desired displacement of the HMV (value of displacement available on our NTN-SNR catalogue).



e Release pressure on the pump in order for the HMV piston to return to its original position. Remove the HMV carefully.

f Check with feeler gauges if required clearance is ok.





Tutorial HMV mounting

To check bearing clearance

- TOOL FEELER GAUGES 100
- TOOL FEELER GAUGES 150 • TOOL FEELER GAUGES 300 Feeler gauge set (length 100, 150, 300 mm)

