INDUSTRY MAINTENANCE TOOLS




www.ntn-snr.com

With You













We provide you a complete solution of tools and services for your bearings, suited to your application, size and resources



NTN-SNR Experts & Tools, at the service of our customers

Because expectations for the maintenance and mounting of bearings are specific to each customer, Experts & Tools offers you solutions that take into account your application and its importance to you as an available resource.

Each application requires special expertise. Maintaining a wind turbine is different to maintaining a printing press or a meat mincer. With the theoretical and practical experience we have accumulated over almost a century of dealing with industrial applications, NTN-SNR can provide you with the expertise and tools you need.

The scale and difficulty of your mounting and maintenance tasks determine our recommendations. We provide a customised response in terms of tools and organisation, suited to your situation.

The NTN-SNR Group, with more than 25,500 employees worldwide, produces and improves maintenance tools and methods on a daily basis. Our aim is to bring you products and procedures that are safe and easy for your staff to use. The design of our tools is aimed at increasing your efficiency.

By reducing the amount of time it takes for mounting, dismounting as well as maintenance operations, and by maximising the working life of your bearings, our tools provide you with real savings and safety in use and will not damage the machinery they are being used on.

This catalogue contains the entire range of NTN-SNR maintenance tools. Our range of greases, greasers and centralised lubrication systems is contained in a separate catalogue.

If you decide to sub-contract your maintenance operations: the Experts & Tools teams can take care of this, based on agreed availability targets for your machinery.

Experts & Tools offers you a range of services that can be customised to meet your specific requirements:

- Theoretical and practical training for your employees.
- Expertise on your damaged bearings (on site or in our laboratories).
- Supervision of the dismounting or mounting of your critical bearings. Of particular interest for larger bearings where we can supply appropriate tools, including handling tools.
- Rental of maintenance tools: induction heaters, hydraulic nuts and pumps, etc.
- Diagnosis of your lubrication installations or an analysis of your needs, with the production and installation of appropriate standard or customised equipment.
- Renovation of bearings removed from equipment as part of a preventive maintenance program.







MAIN CAUSES OF FAILURES OF YOUR BEARINGS

▶ The monitoring of the millions of NTN-SNR bearings sold has allowed us to establish very precise statistics on the origin of faults. This collection of data highlights one essential fact: it is rare that the bearing itself is the cause of a premature failure.

In 90% of cases, the causes can be found in external components which can be classified into four categories:

INAPPROPRIATE LUBRICATION (55%)

Inappropriate or incorrect lubrication significantly reduces the service life of the bearing.

It is often neglected because of bearing accessibility problems and a lack of knowledge about lubricants on the side of the user.

The choice of lubricant, the method, the quantity to apply to the bearing (neither too much nor too little) and the monitoring frequency must be properly studied.

NTN-SNR offers you a special service and markets a complete range of greases covering all applications, as well as an automatic greasing system.

INCORRECT MOUNTING (17%)

The mounting of a bearing on a machine is a key stage in determining the length of its life. A bearing that is not mounted correctly can deteriorate very quickly.

The main causes are:

- Insufficient or poorly adapted methods and resources,
- Contamination during mounting,
- The use of force during mounting,
- Poor preparation of the receiving components: shafts and housings outside tolerance, poor access for the lubricant, misalignment.

Abnormal noise levels can be a warning sign of deterioration. In the short term this causes fatigue of the bearing surfaces. NTN-SNR can provide you with mounting and dismounting services or tools and equipment to make these operations easier and more secure.

POLLUTION (18%)

The environment in which bearings operate is often highly polluted. Dust, liquid detergents, and other contaminants can severely reduce the working life of a bearing.

To deal with these problems, NTN-SNR has developed a comprehensive range of sealing systems and will be pleased to advise you on the best choice for your application.

FATIGUE (10%)

Bearings are key components and are subject to fatigue. Even more so since they rarely operate in ideal conditions (overloaded machine, insufficient lubrication, etc.)

The stresses that active surfaces of bearings are subjected to create surface pitting damage sooner or later.

Our monitoring methods and support from our experts will enable you to act on the first indication of failure and organise appropriate maintenance operations.









GENERALCONTENTS

P.7 MOUNTING & REMOVAL

 Cold mounting 	8
 Hot mounting 	12
 Mechanical dismounting 	17
 Hydraulic mounting and dismounting 	26




P.31 SAFETY & MEASUREMENT

•	Safety instrument	32
•	Measurement instruments	32



P. 35 TECHNICAL DATA



P.54 GLOSSARY

OOL HS (min. size –max. size) / HOOK	Articulated manual ho
PANNER FOOL IFT SET 33 / INDUSTRY FITTING TOOL	Mounting tool kit with
SET 301 / IR THERMOMETER	Infrared thermomete targeting ratio 30 : 1









CONTENTS

MOUNTING & DISMOUNTING

P.8 COLD MOUNTING

•	Mounting tool kit case	9
•	Anti-fretting paste	11
•	Adjustable spanners	11

P. 12 HOT MOUNTING

• Heating equipment 14

P. 17 MECHANICAL DISMOUNTING

•	Bore puller kits	18
•	Deep-groove ball bearings extractor kit	19
•	Self-centering mechanical puller	20
•	Self-centering hydraulic puller	21
•	Case of accessories for hydraulic puller	22
•	Tri-section pulling plate	23
•	Puller - separator kit	24
•	Hydraulic puller for mounting and dismounting	25

P. 26 HYDRAULIC MOUNTING AND DISMOUNTING

•	Hydraulic nuts	28
•	Manual hydraulic pump kits	29
•	Extended tubes	30







MOUNTING & REMOVAL COLD

GOOD PRACTICES FOR COLD MOUNTING

Cold mounting is the simplest method and is suitable for small and medium-sized bearings, completed with the normal adjustments.

OUR RECOMMENDATIONS:

The most frequently observed problems:

- Over- or under-tightening when adjusting.
- Excessive impacts during mounting or forces causing rings and seals to break, or races to become indented.
- The accidental introduction of particles or liquids present in the mounting environment.
- ▶ The bearing must be tightened on the rotating element to which it is fitted. See table below.


	Analysis of rota	ntion (% Incidence)	Retention method
	Fixed housing and load (95%)	Rotating housing and load (0.5%)	
Fixed load with respect to the outer ring			Inner ring tightened on shaft
	Rotating inner ring	Stationary inner ring	
	Stationary shaft and load (3%)	Rotating shaft and load (1.5%)	
Fixed load with respect to the inner ring			Outer ring tight in housing
	Rotating outer ring	Fixed outer ring	

OUR RECOMMENDATIONS TO BE FOLLOWED:

- Check bearing identifying marks against drawings, specifications and procedures.
- Check that bearing seat dimensions and the accuracy of their shape and position correspond to NTN-SNR drawings and specifications.
- Prepare all equipment, tools and parts required before starting assembly.
- Carefully clean and check all parts and devices in the bearing's environment.
- Remove the bearing from its packaging at the last moment in a completely clean working area.
- Never wash it, except in specified exceptional cases. The bearing is protected from oxidation by a light film of oil compatible with all lubricants.
- · Mount the bearing, using the chosen method.
- Lubricate, using a special bearing grease, following the instructions given.
- After mounting and before final start-up, check its operation, so as to detect any possible anomalies (noise, vibrations, temperature, abnormal play, etc.).

IN PRACTICE:

- ➤ The sleeve is mounted by means of impact rings applied against the bearing ring which has the tightest fit. This avoids stressing the rotating body and damaging the bearing.
- ▶ In the case of a long shaft for mounting requiring longitudinal adjustment of the bearing, we prefer using a mechanical sleeve with tapered contact surface associated with a tapered bore bearing.





▶ WHAT THE NTN-SNR EXPERTS HAVE TO SAY:

For easier mounting and to avoid contact corrosion of the shaft or the housing, always use an anti-fretting paste. This thick lubricant helps preserve the quality of parts surfaces subjected to sliding forces. Without this compound, corrosion would progressively cause the fit between bearing and shaft (or housing) to deteriorate, ultimately leading to vibrations and even the premature deterioration of the bearing and its mounting surfaces.

The anti-fretting paste also avoids introducing any pollutant during assembly (metal chips, liquid, etc.)







COLD MOUNTING TOOL KIT CASE

The NTN-SNR tool kit enables the quick, accurate and safe mounting of bearings.





APPLICATIONS

The use of a suitable socket, associated with the mounting sleeve, enables to install the bearing to the desired adjustment. The simultaneous support of the outer and inner rings prevents the risk of deterioration of the races and rotating assemblies. The kit can also be used for assembling other components such as sealing rings, sprockets and pulleys.

) ADVANTAGES

Of light and strong construction for workshop use, this toolbox contains:

33 impact rings:

- · Very robust for a long working life.
- In impact-resistant, synthetic material, avoiding any metal-to-metal contact.
- Ideal for use in conjunction with a press.
- Calibrated for approximately 400 different bearings:
- with bore diameters between 10 and 50 mm
- and with outside diameters between 26 and 110 mm
- Clearly and permanently identified to aid selection.

3 mounting sleeves:

- Light and extremely robust, made of aluminium.
- With a good grip for the hand.
- 1 special dead blow mallet, ensuring optimum impact force is applied.



COMMERCIAL REFERENCE

TOOL IFT SET 33 / Industry Fitting Tool Set

SPARE PARTS (to order)

• Impact ring

TOOL IMPACT RING (tube (A,B,C), socket Example: *TOOL IMPACT RING A 10-25*

• Dead-blow mallet

TOOL IMPACT RING HAMMER

Mounting sleeve

TOOL IMPACT RING SLEEVE (tube A,B,C) Example: TOOL IMPACT RING SLEEVE A

• Socket for mounting sleeve


TOOL IMPACT RING LOOSE RING (tube A,B,C) Example: TOOL IMPACT RING LOOSE RING A





Mounting sleeve


Impact ring






















MOUNTING & REMOVAL COLD

COL	COLD MOUNTING TOOL KIT CASE - TECHNICAL DATA									
Ref. Tubes		Series 60 62 63 64 16 62/63/98	Series 622 623 630	Series 12 22 13 23	Series 72 73	Series 32 52 33 53	Series 213 222 223	Series 10 2 3 22 23	Series C22 C40	Series 42 43
	#									
	10 / 26	629 16100 6000 6200	63000 62200	1200	7200	3200				4200
	10 / 35 12 / 28 12 / 32	6300 6001 16101 6201	62300 63001 62201	2200	7201	5200 3201				4201
Α	12 / 37 15 / 32	6301 16002 6002	62301 63002	2201 1301 2301	7301	5201				4301
	15 / 35 15 / 42	6202	62202 62302	1202 2203 1302 2302	7202 7302	3202 5202 3302 5302		202		4202
	17 / 35 17 / 40 17 / 47	16003 6003 98203 6203 6303	63003 62203 62303	1203 2203 1303	7203 7303	3203 5203 3303		203 2203 303		4302 4203 4303
	20 / 42	16004 98204 6004	63004	2303		5303				
	20 / 47	6204 6304 16005	62204 62304 63005	1204 2204 1304 2304	7204	3204 5204 3304 5306	22205/20	204 2204 304 2304 1005		4204
В	25 / 52	6005 62/22 98205 6205 63/22	62205	1205 2205	7205	3205 5205	22205	205 2205	C2205	4205
	25 / 62 30 / 55	6305 6403 16006 6006	62305 63006	1305 2305	7305	3305 5305	21305	305 2305 1006	C6006	4305
	30 / 62	62/28 98206 6206 63/28 6306	62206	1206 2206 1306	7206 7306	3206 5206 3306	22206 BS2-2206	206 2206 306	C2206	4306
	35 / 62	6404 16007 6007	63007	2306		5306	2306	1007	00007	
	35 / 72 35 / 80 40 / 68	6207 6307 6405 16008	62207 62307 63008	1207 2207 1307 2307	7207 7307	3207 5207 3307 5307	22207 BS2-2207 21307	207 2207 307 2307 1008	C2207	4207 4307
	40 / 80	6008 6208 6308	62208 62308	1208 2208 1308	7208 7308	3208 5208 3308	22208 BS2-2208 21308	208 2208 308	C2208	4208 4308
С	45 / 75 45 / 85	6406 16009 6009 6209	63009 62209	1308 1209 2209	7209	5308 3209 5209	22308 22209 BS2-2209	2308 1009 209 2209	C2209	4209
	45 / 100 50 / 80	6309 6407 16010 6010	62309 63010	1309 2309 1210	7309	3309 5309	21309 22309	309 2309 1010	C4010	4309
	50 / 90	6210 6310	62210	2210 1310 2310	7210 7310	3210 5210 3310	22210 BS2-2210 21310	210 2210 310	C2210	4210 4310
	50 / 110	6408	62310	2310	7310	5310	22310	2310		4310



MOUNTING PASTE – ANTI-FRETTING AGENT

The NTN-SNR mounting paste is specially designed to prevent contact rust, wear and fretting corrosion between 2 metal surfaces.

It is an innovative heavy metal free paste, which is safe for the environment.



SNR

APPLICATIONS

. Contact corrosion, also known as fretting corrosion, appears in assemblies subjected to vibration or very slight slippage or oscillation. It can lead to the serious deterioration of bearings and other machine components and thus make dismounting very difficult.



- Allows slippage for assemblies with play (wheel bearings, vibrating screens, etc.).
- Preserves the quality of the surfaces and the adjustment of mechanical assemblies by preventing contact (fretting)
- · Facilitates the mounting and dismounting of bearings and components such as nuts, bolts, pins, flanges, couplings, fluted shafts, etc.
- · Water and washing resistant.
- Cost saving considering its light density (0.910) and subsequently lower consumption.
- Grease without heavy metals (Zn, Cu, Pb) and powdered graphite.
- Temperature range for use -30°C to +145°C.

COMMERCIAL REFERENCES LUB MOUNTING PASTE / T 60G LUB MOUNTING PASTE / B 500G



ADJUSTABLE SPANNERS

10 spanners for tightening and loosening up to 30 differently sized nuts!





APPLICATIONS

. NTN-SNR adjustable spanners enable the safe and effortless tightening and loosening of all KM, KML and KMK type nuts and also B, TB, BR and TBR precision nuts. They avoid any damage to the nuts or the shaft.

ADVANTAGES


- Made of special tempered steel, these spanners are extremely strong.
- The joint with its spring washer guarantees gentle reliable operation.
- The laser-etched imprint makes them easily and permanently identifiable.
- The hole in the handle makes them easy to store.
- They are adaptable to cover nut diameters from 15 to 180 mm.

Available in two versions: With pins for nuts with holes





TOOL PS (size) / Pin Spanner (with pin) TOOL HS (size) / Hook Spanner (with hook)









MOUNTING & REMOVAL HOT

GOOD PRACTICES FOR HOT MOUNTING

Hot mounting makes it possible, by raising the temperature of a rotating part, to expand the inner ring of a bearing or bore diameter of a sprocket so that it can be fitted over the shaft with ease.

- In the event of a tightly fitting outer ring, prior to the insertion of the bearing, the housing may be made to expand through heating.
- . Conversely, a shaft can also be cooled using liquefied gas in order to facilitate its insertion into the inner ring of the bearing.

NTN-SNR's induction heaters provide the best solution in terms of safety, efficiency and ease of use compared with oil-bath heating, hot plates or ovens.

Heating using a blowtorch is to be prohibited: it generates localised temperatures that alter the hardness of the bearing and so shorten its service life.

PRINCIPLE OF HEATING BY INDUCTION

The device is comprised of a laminated steel core surrounded by a coil with multiple windings. When a current passes through it, this primary coil generates a magnetic field which itself induces an electric current in the bearing (or other steel part), substituted for the secondary coil of an electrical transformer. When a high-intensity, low voltage AC current passes through it, the part heats up quickly; while non-metallic parts and the device itself remain cool.





Induction heating magnetises the part. It is therefore necessary for the heater to demagnetise it at the end of the heating cycle. This avoids steel particles being attracted into the bearing later on.



THE WORDS OF AN NTN-SNR EXPERT:

The temperature should not be too high so as not to modify the characteristics of the steel (maximum 130°C) or the internal components of the bearing

On the other hand, the temperature must be high enough to generate sufficient expansion for the easy installation of the bearing through temporarily loosening

The heating temperature is a function of the ambient temperature, on the other hand, and the fit of the seat on the other.

The mounting of a part onto a shaft or into a housing requires a certain skill for proper alignment. The use of anti-fretting paste facilitates insertion and protects the shaft or housing from fretting corrosion.

Wearing of heat insulating gloves is essential for the safe and comfortable handling of the heated parts.

In the case of heavy parts, help will be required for their handling (use of a textile sling and mobile hoist or even an overhead crane).

SENSITIVE BEARINGS:

Heating too fast and too much can alter the properties of the material and significantly reduce the life of the bearing.

Furthermore, expanding the inner ring too quickly relative to the outer ring, can subject the rolling elements to significant stresses that can lead to their deterioration or that of the raceway.

A function such as the Temperature mode with 2 sensors of SmartTEMP devices makes it possible to control the temperature delta between the rings.



110°C 110°C

PARTS SENSITIVE TO INCREASE IN TEMPERATURE (SPROCKETS):

Some parts like sprocket are extremely sensitive to sudden changes in temperature.

For a sprocket, the teeth are subject to significant mechanical stress (see opposite). Heterogeneous heating in this area can lead to mechanical deformations, and later, to rupture of teeth under stress.

The linear and uniform heating of sensitive parts (Ramp mode) offered by the devices in the SmartTEMP range makes it possible to prevent this risk.



THE RIGHT QUESTIONS TO ASK YOURSELF WHEN SELECTING A HEATING DEVICE

- Type of part to heat (sprocket, bearing, etc.) and its sensitivity.
- How big are the parts to be heated? (Max. external diameter, max. width, min. and max. bore)
- What are the minimum and maximum weights of the parts?
- What temperature has to be achieved?
- What electrical current and voltage are available in the workshop?







THE KEY ADVANTAGES OF THE SMART TEMP RANGE:

SINGLE-POINT HEATING MANAGEMENT

From simple to extremely sensitive part, from the bearing to the sprocket, the NTN-SNR range offers the most suitable solution with real-time heating analysis and control.

Depending on the type of part to be heated, 4 heating modes are available:

- A Temperature mode using a sensor for non-sensitive parts.
- A Time mode that enables to adjust the heating time only.
- A Ramp mode for linear and controlled temperature rise dedicated to sprockets and other parts sensitive to temperature gradients.
- A Temperature mode with 2 sensors to control the temperature delta between inside and outside diameters. Particularly suitable for sensitive bearings.



EASY TO USE

Hot mounting is so simple due to the setting up, management and extraction of data facilitated by an innovative touch screen.

- Simple instructions available in several languages.
- Temperature vs. time graph.
- Extraction of data via USB key.
- Automatic probe detection.
- · Simplified maintenance by self-diagnosis at every start-up.



HIGH PERFORMANCE

The SmartTEMP induction heaters adapt to any type of part, ensuring uninterrupted operation with reduced energy consumption.

- First device to be able to heat a bearing or a solid part of the same weight.
- Better market efficiency thanks to a new state-of-the-art processor (30% time saving compared to standard machines).
- Self-regulation of energy consumption according to the part to be heated.
- Electronics and heat-resistant materials that can ensure intensive and continuous use.



CONTROL AND SAFETY

- Optimum control of the heating cycle by microprocessor and magnetic temperature probe.
- Industrial screen resistant to projections and impacts.
- Thermal insulation of the magnetic probe.
- The equipment uses a default recommended temperature of 110°C.
- Maximum heating temperature: +240°C.
- Maintaining the final temperature when it is reached.
- · Automatic demagnetising at the end of the cycle.
- Only the part to be heated is subjected to an increase in temperature (easier handling, no risk of burning).
- . No emanation of smoke.
- Meets EEC legislative standards.
- · Robust industrial design.







MOUNTING & REMOVAL HOT

HEATING EQUIPMENT





Portable induction heater.

Combines all the features of the SmartTEMP range in a compact device.

Lightweight and easy to use, can heat a part weighing up to 50 kg.



) BENEFITS

- Small, light heater: weighs only 21 kg. 230 V/13 A power supply.
- High performance: Designed for all bearings and rotating parts with a bore diameter above 10 mm with a maximum diameter of 400 mm and a maximum weight of 50 kg.
- Safe: 4 heating modes: Time, Ramp, Temperature (1 sensor), Temperature (2 sensors). Second sensor optional.
- Easy to use: Interactive touch screen enabling precise control of the device (heating settings and graphics). Several languages available.
- Extraction of heating data (USB).

Delivered as standard with its 3 yokes, a pair of gloves and a sensor. (Optional carrying case)

🔷 соми

COMMERCIAL REFERENCE

TOOL SMART TEMP S / induction heater





Induction heater with pivoting yoke, a best-seller for maintenance or production workshops, which can heat a bearing weighing up to **100 kg**.



) BENEFII

- Used as fixed equipment. 230 V/16 A power supply.
- It is **compact**, weighing only 40 kg, and can be easily moved using its 2 side handles.
- High performance: Designed for all bearings and rotating parts with a bore diameter above 10 mm with a maximum diameter of 500 mm and a maximum weight of 100 kg.
- Safe: 4 heating modes: Time, Ramp, Temperature (1 sensor), Temperature (2 sensors). Second sensor optional.
- Easy to use: Interactive touch screen enabling precise control of the device (heating settings and graphics). Several languages available.
- Extraction of heating data (USB).
- Ergonomic with its standard pivoting yoke which facilitates the loading of the parts to be heated.

Delivered as standard with a probe, a pair of gloves and a yoke for bore diameter greater than or equal to 70 mm. Other yoke sizes are available as an option and must be ordered according to the application.



COMMERCIAL REFERENCE

TOOL SMART TEMP M / induction heater



SmartTEMP 📘

Compact induction heater, providing high heating power for parts weighing up to 200 kg.



BENEFITS

- 400 V/20 A power supply.
- High performance: Designed for all bearings and rotating parts with a bore diameter over 20 mm, with a maximum outside diameter of 600 mm and a maximum weight of 200 kg in a horizontal position.
- Safe: 4 heating modes: Time, Ramp, Temperature (1 sensor), Temperature (2 sensors).
- Easy to use: Interactive touch screen enabling precise control of the device (heating settings and graphics).
 Several languages available.
- Extraction of heating data (USB).
- Ergonomic with its standard pivoting arm which facilitates the loading of the parts to be heated.


Delivered as standard with 2 sensors, a pair of gloves and a yoke for bore diameter greater than or equal to 100 mm. Other yoke sizes are available as an option and must be ordered according to the application.

COMMERCIAL REFERENCE

TOOL SMART TEMP L / induction heater

SmartTEMP XL / XL PIVOT

>38





BENEFITS

- 400 V/32 A power supply.
- **High performance**: Designed for all bearings and rotating parts with a bore diameter over **30 mm**, with a maximum outside diameter of **1000 mm** and a maximum weight of **400 kg** in a horizontal position.
- Ergonomic: Available in two versions, with or without pivoting yoke. The pivoting yoke makes the device more suitable for loading medium sized parts while the standard version is particularly suitable for large parts.
- Safe: 4 heating modes: Time, Ramp, Temperature (1 sensor), Temperature (2 sensors).
- Easy to use: Interactive touch screen enabling precise control of the device (heating settings and graphics). Several languages available.
- Extraction of heating data (USB).

Available with pivoting or movable vertical yoke. Possibility to make the device movable with an optional trolley. Delivered as standard with 2 sensors, a pair of gloves and a yoke for bore diameter greater than or equal to 115 mm. Other yoke sizes are available as an option and must be ordered according to the application.

COMMERCIAL REFERENCE

TOOL SMART TEMP XL (/ XL PIVOT) / induction heater



39

Very powerful induction heater for parts weighing up to **800 kg**, typically for heavy mechanical workshops (steelworks, paper mills, gear manufacturing, naval yards, etc.).



BENEFITS

- 400 V/63 A power supply.
- **High performance**: Designed for all bearings and rotating parts with a bore diameter over **40 mm**, with a maximum outside diameter of **1500 mm** and a maximum weight of **800 kg** in a horizontal position.
- Safe: 4 heating modes: Time, Ramp, Temperature (1 sensor), Temperature (2 sensors).
- Easy to use: Interactive touch screen enabling precise control of the device (heating settings and graphics). Several languages available.
- Extraction of heating data (USB).
- Ergonomic: the yokes are positioned vertically and are equipped with a lifting ring. An optional lifting device simplifies handling

Possibility to make the device movable with an optional trolley.

Delivered as standard with 2 sensors, a pair of gloves, a yoke for bore diameter greater than or equal to 145 mm.

Other yoke sizes are available as an option and must be ordered according to the application.

COMMERCIAL REFERENCE

TOOL SMART TEMP XXL / induction heater





MOUNTING & REMOVAL HOT

SmartTEMP XXXL

> 39

Extremely powerful induction heater for parts weighing up to 1600 kg.

Essential in machine shops of steelworks, paper mills and the rail and wind turbine sectors.



NTN ENT

BENEFITS

- 400 V/100 A power supply.
- High performance: Designed for all bearings and rotating parts with a bore diameter over 85 mm, with a maximum outside diameter of 2000 mm and a maximum weight of 1600 kg in a horizontal position.
- Safe: 4 heating modes: Time, Ramp, Temperature (1 sensor), Temperature (2 sensors).
- Easy to use: Interactive touch screen enabling precise control of the device (heating settings and graphics).
 Several languages available
- Extraction of heating data (USB).
- Ergonomic: the yokes are positioned vertically and are equipped with a lifting ring. An optional lifting device simplifies handling.

Delivered as standard with 2 sensors, a pair of gloves and a yoke for bore diameter greater than or equal to 215 mm. Other yoke sizes are available as an option and must be ordered according to the application.

COMMERCIAL REFERENCE

TOOL SMART TEMP XXXL / induction heater



A lifting device is offered for use with the SmartTEMP XXL and XXXL.



COMMERCIAL REFERENCE

TOOL ST/ (Size of the device) LIFTING DEVICE, e.g. TOOL ST/XXL LIFTING DEVICE

Trolleys may be used to make SmartTEMP XL, XL Pivot, XXL movable.

Adapted to each model and delivered as an option. Can be ordered separately for XL/ XL Pivot series. Trolley for XXL and XXXL has to be ordered at the same time as the heater.

COMMERCIAL REFERENCE

TOOL ST/(Size of the device) TROLLEY, e.g. TOOL ST/XL TROLLEY

Yokes and Extension yokes are available to meet the specific requirements related to the diameters of the part to be heated.





For each SmartTEMP model, a suitable set of yokes and extension yokes is available as an option.

OMMERCIAL REFERENCE

Yokes: TOOL ST/ (Size of the device) YOKE (Bore diameter capacity), e.g. TOOL ST/XXL YOKE 60

Extension yokes: TOOL ST/ (Size of the device) EXTENSION YOKE (extension height),

e.g. TOOL ST/L EXTENSION YOKE 150

SPECIAL PRODUCTS

This device, especially developed for a wind turbine application, is capable of heating parts weighing up to 10 tonnes with an outside diameter of 4 metres to 120°C in 60 minutes.

NTN-SNR is able to design machines, specially adapted to your application.

The dimensions and performance of our induction heaters can be modified to match precisely the **geometry of your parts**, your **production rates** and the **electrical supply available** in your workshops.

Customised equipment can also be developed for your very large metal parts, used for wind turbine and railway applications. We can provide you with an accurate quotation based on the following information:

- The weight of the part to be heated (min./max.)
- Dimensions of the part (min./max. bore, max. outside diameter, max. width)
- Electrical power and voltage available.
- Temperature to be achieved.

With You

• Desired heating time or production pattern.







MOUNTING & REMOVAL MECHANICAL

GOOD PRACTICES FOR MECHANICAL DISMOUNTING

Take care when dismantling: look after your equipment and save time, while working safely.

Note, the dismounting of bearings is a delicate operation, both for the operator and for the mechanical items involved.

If mounting requires a lot of know-how, the risks involved in dismounting cannot be ignored, even if the bearing is to be scrapped.

By opting for the correct methods and tools, you reduce the risk of personal injury and damaging parts (shaft, housing, even the bearing, if it is to be re-used).


The two main principles for dismounting are mechanical and hydraulic.


OUR RECOMMENDATIONS FOR MECHANICAL DISMOUNTING

Whenever possible; apply the withdrawal force to the ring with the interference fit.

There are numerous types of extractor, depending on the grip offered by the bearing, its accessibility and the extraction force required.

Extractors equipped with a pump and hydraulic cylinder allow the operator to develop very high extraction efforts, using their own muscular strength. They are easy to use, due to the fact that their arms are self-centering.





THE PROPER QUESTIONS TO BE ASKED

- How do I grip the part?
 Selection of the type of grip: external, internal or special.
- What is the diameter of the part to be extracted? Enables the span, spread and force to be defined.
- How do I pull on the part?
 Choice of a support point: on the central shaft, on the outside of the part or using extraction accessories.







MOUNTING & REMOVAL MECHANICAL

BORE PULLER KITS

Puller kits for internal gripping of the bore. For quick and easy dismounting of bearings tightly mounted in a housing.





APPLICATIONS

Ideal selection of high-strength extractors with braces for extraction via the bore:

- Bearing whose outer ring is a tight fit in its housing.
- Outer rings or rings with well locked packing.

ADVANTAGES

Practical

- The BP Set 5-44 has a thrust bolt fitted with a handle facilitating the grip for the hand, as well as a slide hammer.
- Each kit contains several pullers that adapt to each of your applications.
- The case for small bearings combines an adjustable counter support and a slide hammer offering you the choice of extraction mode.

Reliable and safe

- The unique design of adjustable puller blocks enables successful and safe dismounting, without risk of jacking over and without forces.
- Each part is made of high quality steel, robust and resistant to impact, ensuring product longevity.

Flexible

- BP Set 5-44 includes 7 pullers for extractions of 5 to 44 mm bore diameters.
- BP Set 45-100 includes 3 pullers for extractions of 45 to 100 mm bore diameters.



TOOL BP Set 5-44 / Bore puller set TOOL BP Set 45-100 / Bore puller set




BP Set 45-100











DEEP-GROOVE BALL BEARINGS PULLER KIT

For quick and easy extraction of your deep-groove ball bearings housed in blind bearings.





BBPS 10-100

APPLICATIONS

This puller kit is specially adapted to carry out, without dismantling your machine, extractions of bearings that are difficult to access, such as:

- Bearings housed in blind bearings,
- Bearings installed on shafts,
- Bearings with a tight fit on outer or inner rings.

ADVANTAGES

Practical and easy

- The kit contains 3 o-rings to facilitate the assembly of your tool.
- The marking of parts along with the selection table included enables a quick selection of accessories to be used.
- The visual user guide favours the correct implementation of the tool.

Reliable and safe

- The design of tools enables successful and safe dismounting, without risk of jacking over and without forces.
- Each component is made of high quality steel, robust and resistant to impact, ensuring product longevity.

Flexible


- The case includes 3 different sizes of shafts and 28 puller arms providing a very wide range of applications.
- The kit enables extraction of bearings of 10 to 100 mm bore diameter.



TOOL BBPS 10-100 / Ball bearing puller set



Prong







MOUNTING & REMOVAL MECHANICAL

2/3 JAWS SELF-CENTERING MECHANICAL PULLER

A simple, robust and efficient range of pullers for an easy and safe dismounting of small or medium size bearings.





) APPLICATIONS

Is also well suited to removing pulleys, toothed wheels, flywheels fixed to a shaft.

ADVANTAGES

Practical

- The self-centering mechanism ensures the simultaneous positioning of the puller's arms on the bearing.
- Compact and ergonomic, it may be easily operated in every position by one person.

Safe

- · Self-locking system prevents the arms from bending or slipping.
- The greater the extraction force, the tighter the jaws grip the part.
- Robust, designed in hardened steel for maximum strength.

Multiple uses

- Quickly convertible to two or three claws, depending on the space available.
- Three available models for selection according to the outside diameter of the parts to be extracted and the required reach.

Maximum spread (mm)	Maximum span (mm)	Capacity (tons)
120	80	2
180	120	3
270	160	5




SCMP - 3 arms

OMMERCIAL REFERENCE

TOOL SCMP 2/3-120 / Self-center mech puller TOOL SCMP 2/3-180 / Self-center mech puller TOOL SCMP 2/3-270 / Self-center mech puller













2/3 JAWS SELF-CENTERING HYDRAULIC PULLER



A range of powerful tools for very easy and risk-free dismounting of large bearings and press fitted parts such as pulleys and toothed wheels.

43

APPLICATIONS

The self-centering device facilitates positioning and anchoring around the bearing. The power developed by the hydraulic system allows the part to be extracted safely with very little effort.

ADVANTAGES

Practical

- Ready-to-use in a strong case. No assembly of the jaws required before use.
- Compact: the hydraulic pump is built-in. No need for a separate pump, hose or spindle.
- Ergonomic: pump handle pivoting through 360°, allowing the extractor to be used in the most comfortable position. Telescopic, it provides optimum transmission of the effort.
- Easy centering of the piston on the shaft with retractable, integrated point.
- A piston extension is supplied for use with a remote support surface.
- A piston return device makes it immediately ready for further use.
- Long stroke of hydraulic spindle facilitates dismounting in one operation.

Multiple uses

- Possibility to change between two or three jaws, depending on the accessibility of the bearing.
- Available in four versions, depending on the power and size required: 4, 12, 20 and 30 tons.

Capacity (tons)	Maximum spread (mm)	Maximum span (mm)	Cylinder stroke (mm)
4	325	190	60
12	485	305	85
20	570	365	111
30	680	465	111

• For the 4 and 12-ton capacity, an accessory kit consisting of a puller block, connecting rods and a set of bearings separators increases the number of uses and makes separation easier.

Safe

- · A safety relief valve prevents any risk of overloading and limits the force applied to the maximum capacity of the equipment.
- A cover protects the user from possible flying bearing fragments. Made of transparent material, it provides good visibility for controlling the extraction.
- The 20 and 30-ton model is equipped with an innovative two-stage pump which makes operation easier and safer.



SCHP 4T - 3 arms



SCHP 4T - 2 arms

COMMERCIAL REFERENCE

TOOL SCHP 4 TONS / Self-center hyd puller TOOL SCHP 12 TONS / Self-center hyd puller TOOL SCHP 20 TONS / Self-center hyd puller TOOL SCHP 30 TONS / Self-center hyd puller











MOUNTING & REMOVAL MECHANICAL

ACCESSORY CASES FOR 4 AND 12-TON SCHP

A strong grip for a safe and easy dismounting.





APPLICATIONS

A separator is a complementary tool to a claw extractor when the latter does not have sufficient grip. A perfect grip on the back of parts, using bevelled blades, reduces the force necessary for dismounting and avoids damaging the shaft's contact surface

ADVANTAGES

- Robust design ensuring a long life for the separation blades.
- After separation by tightening the two blades, turning the separator enables greater force to be used without deforming the blades for the complete extraction of the part.
- Extensions are included to compensate for the distance of the support face.
- Easy centering of the piston on the shaft with integrated point.
- Two versions are available depending on the required power: 4 and 12 tons.

COMMERCIAL REFERENCE

TOOL AS-SCHP 4T / acc set hyd puller TOOL AS-SCHP 12T / acc set hyd puller



AS-SCHP 4T



UNIVERSAL, TRI-SECTION PULLING PLATE

A strong grip for safe and effective dismounting using a mechanical or hydraulic puller.





) APPLICATIONS

The tri-section pulling plate is the complementary tool to the three-armed pullers when the latter does not have sufficient grip. Universal, it is suitable for both the SCHP hydraulic extractor and the SCMP mechanical model.

ADVANTAGES

- The blades are placed behind the bearing, where the extraction force is most effective.
- The application of the effort on the inner ring minimises the risk of damaging the bearing while preserving the rolling body and the outer ring.
- The tri-section construction distributes the extraction force evenly, preventing the bearing from locking and/or tilting on the shaft during dismounting.



COMMERCIAL REFERENCE

TOOL BP3S 26-160 / Tri-section back puller TOOL BP3S 50-210 / Tri-section back puller TOOL BP3S 90-340 / Tri-section back puller TOOL BP3S 140-495 / Tri-section back puller







MOUNTING & REMOVAL MECHANICAL

PULLER-SEPARATOR KIT

For easy and risk-free removal of rings or complete bearings mounted on a shaft and difficult to grasp.



Adjustable arms, provided in the kit, also enable extractions by internal or external gripping.



APPLICATIONS

Allows the extraction of all parts mounted onto a shaft by force, such as pulleys, handwheels and sprockets. In order to adapt to your various applications, the adjustable arms will also enable you to dismount:

- Bearings or rings mounted on the shaft (external gripping),
- Bearings or rings jammed in a housing (internal gripping).

ADVANTAGES

2-in-1 tool

- Each case contains a puller block that allows the mounting of the tool for separations as well as extractions.
- The removable arms will allow you to carry out extractions by internal or external gripping.
- A separator for your parts installed on the shaft, as well as a set of removable arms for internal or external gripping, all contained in a single case.

Powerful and reliable

- The separator is equipped with bevelled blades that ensure excellent grip and thereby avoid any locking.
- With a power of 100 kN, BPES guarantees safe extractions without any degradation to your environment.
- The separator as well as the puller are made of very high quality steel, ensuring the resistance and longevity of your kit.

Practical

- Thanks to its unique design, BPES 10-105 covers a wide range of applications.
- The kit contains 2 extensions for applications requiring a long span.

COMMERCIAL REFERENCE

TOOL BPES 10-105/Back puller extract set





Extraction with separator



External grasping extraction





HYDRAULIC PULLER FOR MOUNTING AND DISMOUNTING



Practical and safe 3-in-1 tool, for mounting and dismounting of bearings and sleeves by internal or external grasping.



APPLICATIONS

Ideal tool for mounting and dismounting a large variety of mounting parts, including bushings, bearings, wheels, gears and pulleys.

The kit, supplied in a steel case, includes:

- An internal gripping puller,
- A double-acting hydraulic cylinder: 8 tons for thrust and 12 tons for extraction,
- 3 arms as well as 3 extensions.

) ADVANTAGES

Quick and practical

- 3-in-1 tool for a reduced preparation time: same tool used for mounting and dismounting of bearings.
- The single double-acting cylinder ensures a thrust force of 8 tons as well as an extraction of 12 tons.
- Included extensions can be used to attain a greater range.

Longevity

• A built-in safety valve enables the tool to operate below rated pressure in order to preserve it over time.

Safety

- The built-in safety valve prevents all injuries to the user and all damage to the working environment.
- A self-centering design avoids risk of slipping of the arm during the extraction operation by internal gripping.

COMMERCIAL REFERENCE

TOOL PUSH/PULLER 8/12 Tons



Internal gripping



Extraction



Thrust







MOUNTING & REMOVAL HYDRAULIC

THE GOOD PRACTICES FOR HYDRAULIC MOUNTING AND DISMOUNTING

HYDRAULIC MOUNTING


The mounting of large bearings with tapered bores requires considerable effort that is difficult to produce by mechanical screw tightening. The use of hydraulic technology is required in such cases.


A preliminary solution consists in injecting an oil film over the entire contact area between the shaft and the inner ring. Another solution consists in using a hydraulic nut to develop the necessary mounting force.

The two principles may also be used simultaneously to make mounting easier. The residual clearance is checked using feeler gauges or a dial gauge is used to measure the displacement of the bearing along the tapered seat.


Two types of mounting lend themselves to this method:


TAPERED SEAT SHAFT





SHAFTS WITH A CYLINDRICAL CONTACT SURFACE IN ASSOCIATION WITH A SLEEVE












HYDRAULIC DISMOUNTING

- If an adapter or withdrawal sleeve was used during mounting, a hydraulic nut can be used for quick and effortless dismounting.
- If hydraulic channels were originally provided in the shaft, the injection of a film of oil on the contact surface between the shaft and the inner ring greatly reduces the effort required.















MOUNTING & REMOVAL HYDRAULIC

HYDRAULIC NUTS

Precise, effortless mounting of your large bearings with a tool that is always ready for use.





APPLICATIONS

Beyond a certain shaft diameter, the mounting or dismounting of a bearing on tapered seatings requires hydraulic assistance.

A hydraulic nut ensures perfect control of the adjustment of the assembly while limiting the use of manual force and reducing the time taken for the operation.

ADVANTAGES

Besides the hydraulic principle, the "back and forth" design provides unique ease of operation with the automatic return of the thrust plate to its initial position (design patented by NTN-SNR)

"No need to retract the piston manually. This operation is often tedious and subject to oil leaks: the NTN-SNR nut is automatically ready for a new use."



- Range also available in standard inch dimensions HMVC from 1,967 to 37,410 inches.
- Special sizes on request.
- Set of spare piston seals supplied as standard.
- The hydraulic nut is equipped with:
 - Two hydraulic connection points, with spot facing for perfect sealing,
- One quick coupling connection (male) which can be positioned on the front face or on the outside diameter, depending on the ease of access.
- (The 1500 bar high pressure provides maximum safety with a locking stop),
- One 1500 bar ball valve,
- 3 holes in the front face are provided for mounting the dial gauge (not included).
- The surface treatment of the nuts provides excellent protection against corrosion and ensures a long working life.
- Easier handling and nut screwing due to:

TOOL HMV (size) EBF / Hydraulic nut (metric)
TOOL HMVC (size) EBF / Hydraulic nut (inches)

- The knurling of the outer surface,
- A bar being supplied and the provision of 4 holes on the outer diameter. (For sizes ≥ HMV 50 EBF).
- Easy handling with eye bolts for nut sizes HMV 60 EBF and upwards supplied.

Tool Dial gauge 50



OPTIONAL ACCESSORIES

COMMERCIAL REFERENCE

• Dial gauge for the measurement of the displacement of the piston from 5 to 10mm

COMMERCIAL REFERENCE

- TOOL DIAL GAUGE 50
- TOOL DIAL GAUGE 100
- Adaptor kit for the dial gauge

COMMERCIAL REFERENCE

- TOOL DIAL EXTENSION SET

MANUAL HYDRAULIC PUMP KITS

A two-stage, high-pressure, ultra-light hand pump, 700 bar (70 mPa) 0.3 L and 0.9 L with 2 stages.



APPLICATIONS

These high-pressure pumps are designed for use with automatic return hydraulic nuts or for the mounting and dismounting of bearings coated with an oil film.

Pumps are supplied as standard with the following accessories designed for use at 700 bar:

- 1 pressure gauge, minimising the risk of overloading,
- 1 high-quality hose (1.5 m for the 700 bar pump with a 0.3 litre reservoir, 3m for the 700 bar pump with a 0.9 litre
- 1 quick coupling connection (female) suitable for NTN-SNR hydraulic nuts,
- They are supplied filled with hydraulic oil.



- Ultra-light, compact design.
- Robust reservoir in composite materials.
- Ergonomic: locking of the lever to facilitate transport.
- Robust: pump guaranteed for life under normal conditions of use.
- Efficient: savings in time and effort due to the two stages which allow a reduction of 80% in the number of pump strokes required in comparison with single-stage pumps.
- User safety: electrically isolated lever and safety relief valve.
- Multiple uses: 3 available reservoir sizes:
 - 0.3 litre for nuts ≤ HMV 54 EBF,
 - 0.9 litre for nuts ≤ HMV 92 EBF,
 - For sizes > HMV 92 EBF, contact us.

Accessories included for 700 bar pump

- Pressure gauge adaptor for pumps 750b 0.3L and 0.9L.
- Pressure gauge (0-700 bar) or (0-1500 bar)
 - Liquid filled to protect against any sudden loss of pressure,
 - Dual markings in bars / PSI,
 - Fitted with a device protecting against bursting.
- - Very strong thermoplastic, reinforced with layers of woven steel wire,
 - Polyurethane envelope for extreme abrasion resistance,
 - With a rubber protective "handle".
- · Quick coupling protection (female) 1500 bars, which provides maximum safety with end stop locking and optimum sealing with a flat face valve.

Technical characteristics of the hydraulic oil

Contains corrosion inhibitors which do not attack sealing materials such as nitrile.

Relative density at 15°C: 0.870 kg/dm³

Viscosity at 40°C: 31 cSt Viscosity index: 102

Flash point: 230°C Freezing point: -36°C

COMMERCIAL REFERENCE

TOOL PUMP SET 700B - (reservoir capacity) I / Pump with accessories TOOL HYDRAULIC OIL 1 L



TOOL PUMP SET 700B



TOOL HYDRAULIC OIL 1L







MOUNTING & REMOVAL HYDRAULIC

EXTENSION TUBES AND THEIR ADAPTORS

In order to allow pressurised oil injection into a sleeve or a shaft with a thick wall, NTN-SNR proposes a range of extension tubes with adaptors, thus enabling to facilitate the extraction of a bearing.

- Maximum pressure = 1500b for greater safety.
- Stainless steel tubes for very high resistance.

Pipe

Several sizes available. It can be connected directly to the sleeve.

Adaptor

To be selected according to the extension tube diameter. It enables to connect the tube to the hydraulic connection (not supplied with the adaptor).

Pipe

Connection

It is screwed onto the adaptor (G1/4) and can be directly used with our pump kits, T00L PUMP set 700b and 1500b.





Adaptor


Connection


Sizes and references

Sleeve threading	Pipe	Adaptor	Connection
M4 (diagram 1)	TOOL EXTENSION PIPE M4 50 MPA	TOOL CONNECTING NIPPLE M4 150 MPA	
M6 (diagram 2)	TOOL EXTENSION PIPE M6 150 MPA	TOOL CONNECTING NIPPLE M6 150 MPA	TOOL
G 1/8 (diagram 3)	TOOL EXTENSION PIPE G1/8 150 MPA	TOOL CONNECTING NIPPLE G1/8 150 MPA	HMV NIPPLE 1/4
G 1/4 (diagram 4)	TOOL EXTENSION PIPE G1/4 150 MPA	TOOL CONNECTING NIPPLE G1/4 150 MPA	













With You



CONTENTS

SAFETY & MEASUREMENT

P. 32 SAFETY INSTRUMENT

Heat-resistant gloves

P. 32 MEASUREMENT INSTRUMENTS

Set of calibrated feeler gauges
Infra-red thermometer with laser targeting
33



32





SAFETY & MEASUREMENT

SAFETY INSTRUMENT

HEAT-RESISTANT GLOVES

Protective gloves to safely handle oily and hot parts of up to +350° C.





ADVANTAGES

- Made of KEVLAR, they are extremely resistant to tearing, abrasion and cuts.
- Non-inflammable: they provide a high level of protection against contact and convective heat.
- They are tested and certified for mechanical (EN 388) and thermal (EN407) hazards.
- Non-fluffy, they avoid polluting the bearings.
- Extremely comfortable, they are useful for all maintenance work.
- Single size: 10.5.

COMMERCIAL REFERENCE

TOOL GLOVE HEAT RESISTANT

MEASUREMENT INSTRUMENTS

SET OF CALIBRATED FEELER GAUGES

A simple and precise tool for measuring the clearance between two parts.





APPLICATIONS

This feeler gauge set allows the quick, accurate measurement of radial clearance, especially on spherical roller and cylindrical bearings. It contains 17 gauges.


3 versions of the gauge set are offered: 100mm, 150mm and 300 mm long.

ADVANTAGES

- Set of 17 round end gauges.
- Delivered with a spare set of the thinnest gauge blades.
- Available in 100 mm, 150 mm and 300 mm.
- In a protective steel sleeve.
- Calibrated to 1/100th.

COMMERCIAL REFERENCE

FEELER GAUGE TOOL (gauge length)







LASER TEMP 301 INFRA-RED THERMOMETER WITH LASER TARGETING



Enabling a preliminary diagnosis of the machine operation by means of accurate and safe measurement of the temperature remotely or by contact.



APPLICATIONS

The LASER TEMP 301 thermometer combines safety with accuracy.

- The safety of remote infrared measurement for burning, moving or difficult-to-access objects.
- Accurate measurement using the contact probe.
 Its elaborate optical system allows small, remote targets to be measured easily and precisely.

ADVANTAGES


- Wide measurement range in infrared mode: -50°C to +850°C.
- High degree of precision, using the:
 - Laser targeting device,
 - The excellent 30:1 distance:target ratio,
 - Emissivity adjustable between 0.1 and 1,
 - Type K thermocouple wire probe.
- Extremely quick measurements: response time less than 1 second.
- Internal memory able to record up to 20 measurements.
- Equipped with the following functions:
 - High / low, visual and audible adjustable alarms,
 - Automatic switch-off to maximise its useful life,
 - Maximum, minimum, difference, average measurement.
- Light, ergonomic gun shape.
- Simple to use, it may be easily configured to work in °C or °F.
- Back-lit display for easy reading.

Supplied with:


- Type K thermocouple wire probe (range -50°C to +440°C, length 1 m),
- Protective pouch User manual.

COMMERCIAL REFERENCE

TOOL LASERTEMP 301 / IR Thermometer



Principle




Distance / Target











CONTENTS

TECHNICAL DATA

 Mounting tool kit case 	36
Anti-fretting paste	36
 Adjustable spanners 	36
 Heating equipment 	38
Bore puller kits	41
 Deep-groove ball bearings extractor kit 	42
 Self-centering mechanical puller 	43
 Self-centering hydraulic puller 	43
 Accessory cases 	44
 Tri-section pulling plate 	44
 Puller - separator kit 	45
 Hydraulic puller for mounting and dismounting 	45
 Hydraulic nuts 	46
 Manual hydraulic pump kits 	50
 Heat-resistant gloves 	52
 Set of calibrated feeler gauges 	52
 Infra-red thermometer with laser targeting 	53



TECHNICAL DATA

COLD MOUNTING TOOL KIT CASE	> P 9	
Reference	TOOL IFT SET 33 / Industry Fitting Tool Set	
Description	Mounting tool kit	
Application	Cold mounting of bearings: bore Ø: 10 to 50 mm outside Ø: 26 to 110 mm	
Contents	 33 Impact rings 3 Mounting sleeves 1 Dead-blow mallet (weight 0.7 kg) 	
Material	Socket machined from strong, solid material	
Case dimensions	430 x 320 x 100 mm	
Weight of kit, including case	4.8 kg	

ANTI-FRETTING PASTE B 500G / T 60G	> P 11
References	LUB MOUNTING PASTE
Density	0.910
Colour	Brown
Texture	Smooth
Nature of thickener	Aluminium complex
NLGI consistency	1.5
Temperature range for use	-30°C to +145°C
Drop point NF T 60102C	> 240°C
Packaging	Tube 60 g – box 500 g

ADJUSTABLE SPANNERS		≻ P 11		
Reference	TOOL PS (size) / Pin spanner			
Description	Articulated manual pin spanner	Articulated manual pin spanner		
Material	Hardened, forged chrome vanadium steel. Satin chrome finish	Hardened, forged chrome vanadium steel. Satin chrome finish		
Pin hardness	40 HRC	40 HRC		
Use	Tommy nuts (examples of accuracy: TB, T	Tommy nuts (examples of accuracy: TB, TBR, TBP, TBPR, etc.)		
References	Nut diameter (mm)	Pin diameter (mm)		
T00L PS 15-35	15-35	3		
TOOL PS 35-50	35-50	4		
TOOL PS 50-80	50-80	5		
TOOL PS 80-120	80-120	6		
T00L PS 120-180	120-180	8		
References	TOOL HS (size) / Hook spanner	TOOL HS (size) / Hook spanner		
Description	Articulated manual hook spanner	Articulated manual hook spanner		
Material	Hardened, forged chrome vanadium steel. Satin chrome finish	Hardened, forged chrome vanadium steel. Satin chrome finish		
Use	Slot nuts (e.g.: KM, KML,, B, BR, BP,)	Slot nuts (e.g.: KM, KML,, B, BR, BP,)		
References	Nut diameter (mm)			
TOOL HS 15-35	15-35	15-35		
TOOL HS 35-50	35-50	35-50		
TOOL HS 50-80	50-80	50-80		
TOOL HS 80-120	80-120	80-120		
TOOL HS 120-180	120-180	120-180		



	PRECISIO	ON NUT CROSS	REFERENCE/	tommy nut ar	nd slot nut sp	anners				
	Spanner 1	15-35 (mm)	Spanner 3	35-50 (mm)	Spanner 5	50-80 (mm)	Spanner 8	0-120 (mm)	Spanner 12	20-180 (mm)
	Hook	Pin	Hook	Pin	Hook	Pin	Hook	Pin	Hook	Pin
	B 20/1	B 20/1	B 25	TB 25	B 35	TB 35	B 60	TB 60	B 90	TB 90
	TB 90	B 20/1.5	B 30	TB 30	B 40	TB 40	B 65	TB 65	B 95	TB 95
nuts	-	-	-	-	B 45	TB 45	B 70	TB 70	B 100	TB 100
B and TB nuts	-	-	-	-	B 50	TB 50	B 75	TB 75	-	-
B an	-	-	-	-	B 55	TB 55	B 80	TB 80	-	-
	-	-	-	-	B 60	TB 60	B 85	TB 85	-	-
	-	-	-	-	-	-	B 90	TB 90	-	-
	-	-	BP 20/1	TBP 20/1	BP 30	TBP 30	BP 55	TBP 55	BP 75	TBP 75
ants	-	-	BP 20/1.5	TBP 20/1.5	BP 35	TBP 35	BP 60	TBP 60	BP 80	TBP 80
BP and TBP nuts	-	-	BP 25	TBP 25	BP 40	TBP 40	BP 65	TBP 65	BP 85	TBP 85
and 1	-	-	-	-	BP 45	TBP 45	BP 70	TBP 70	BP 90	TBP 90
B B	-	-	-	-	BP 50	T BP 50	-	-	BP 95	TBP 95
	-	-	-	-	-	-	-	-	BP 100	TBP 100
	-	-	BR 25	TBR 25	BR 35	TBR 35	BR 60	TBR 60	BR 90	TBR 90
S	-	-	BR 30	TBR 30	BR 40	TBR 40	BR 65	TBR 65	BR 95	TBR 95
BR and TBR nuts	-	-	-	-	BR 45	TBR 45	BR 70	TBR 70	BR 100	TBR 100
d TBF	-	-	-	-	BR 50	TBR 50	BR 75	TBR 75	-	-
3R an	-	-	-	-	BR 55	TBR 55	BR 80	TBR 80	-	-
	-	-	-	-	BR 60	TBR 60	BR 85	TBR 85	-	-
	-	-	-	-	-	-	BR 90	TBR 90	-	-
	-	-	BPR 20/1	TBPR 20/1	BPR 30	TBPR 30	BPR 55	TBPR 55	BPR 75	TBPR 75
nuts	-	-	BPR 20/1.5	TBPR 20/1.5	BPR 35	TBPR 35	BPR 60	TBPR 60	BPR 80	TBPR 80
BPR and TBPR nuts	-	-	BPR 25	TBPR 25	BPR 40	TBPR 40	BPR 65	TBPR 65	BPR 85	TBPR 85
and	-	-	-	-	BPR 45	TBPR 45	BPR 70	TBPR 70	BPR 90	TBPR 90
BPR	-	-	-	-	BPR 50	TBPR 50	-	-	BPR 95	TBPR 95
	-	-	-	-	-	-	-	-	BPR 100	TBPR 100


Spanner 15-35 (mm)	Spanner 35-50 (mm)	Spanner 50-80 (mm)	Spanner 80-120 (mm)	Spanner 120-180 (mm
T00L HS 15-35	T00L HS 35-50	T00L HS 50-80	T00L HS 80-120	T00L HS 120-180
KM 0	KM 5	KM 7	KM 12	KM 18
KM 1	KM 6	KM 8	KM 13	KM 19
KM 2	-	KM 9	KM 14	KM 20
KM 3	-	KM 10	KM 15	KM 21
KM 4	-	KM 11	KM 16	KM 22
-	-	KM 12	KM 17	KM 23
-	-		KM 18	KML 24
-	-	-	-	KM 24
-	-	-	-	KM 25
-	-	-	-	KML 26
-	-	-	-	KML 27
-	-	-	-	KML 28
-	-	-	-	KML 28





HEATING APPARATUS - TOOL SmartTEM	IP (SIZE) / INDUCTION HEATER	R		➤ P 14/15
TECHNICAL DATA	SmartTEMP S	SmartTEMP M	SmartTEMP L	SmartTEMP XL / XL Pivo
ELECTRICITY				
Maximum power consumption	3 kVA	3,7 kVA	8 kVA	12,8 kVA
Maximum voltage/current	230 V / 13 A	230 V / 16 A	400 V / 20 A	400 V / 32 A
Frequency	50 Hz	50 Hz	50 Hz	50 Hz
Other voltages on request	110 V - 240 V	110 V - 240 V	480 V - 575 V	480 V - 575 V
Other frequencies on request	60 Hz	60 Hz	60 Hz	60 Hz
CONTROL				
Temperature adjustment	+40°C à +240°C (+400°C opt.)	+40°C à +240°C (+400°C opt.)	+40°C à +240°C (+400°C opt.)	+40°C à +240°C (+400°C opt.)
Heating time adjustment Maximum temperature Δ Temperature	0-99 hours +240°C 20-50°C	0-99 hours +240°C 20-50°C	0-99 hours +240°C 20-50°C	0-99 hours +240°C 20-50°C
Temperature probe Reference: Tool +	1 (2 in option) TEMP PROBE 400°	1 (2 in option) TEMP PROBE 1000*	2 TEMP PROBE 1000*	2 TEMP PROBE 1000*
Heating modes - Time - Ramp - Temp. with 1 sensor - Temp. with 2 sensor	•	•	•	•
Temperature control precision	+/-2°C	+/-2°C	+/-2°C	+/-2°C
Temperature holding at the end of cycle	•	•	•	•
Demagnetising	Automatic	Automatic	Automatic	Automatic
Residual magnetism	< 2 A / cm	< 2 A / cm	< 2 A / cm	< 2 A / cm
Audible signal	•	•	•	•
APPLIANCE DESIGN				
Dimensions (L x W x H) (mm)	450 x 210 x 275	540 x 275 x 365	695 x 330 x 475	850 x 410 x 1050
Space between pivots A and B (1)	120 x 145 mm	180 x 180 mm	210 x 215 mm	300 x 324 mm / 330 x 300 mm (XL Pivot)
Weight (without yoke)	21 kg	40 kg	85 kg	157 kg
Pivoting arm	no	•	•	• (XL Pivot)
Trolley (optional)	no	no	no	•
PARTS TO BE HEATED				
Maximum weight	50 kg	100 kg	200 kg	400 kg
Minimum bore diameter with smallest yoke.	10 mm	10 mm	20 mm	30 mm
Maximum external diameter	400 mm	500 mm	600 mm	1000 mm
Maximum width	140 mm	180 mm	210 mm	315 mm / 320 mm (XL Pivot)

 $^{^{\}star}$ length of probe wire (e.g. 400: 400 = 400 mm)








HEATING APPARATUS - TOOL SmartTEMP (SIZE) / INDUCTION HEATER	➤ P 15/16
TECHNICAL DATA	SmartTEMP XXL	SmartTEMP XXXL
ELECTRICITY		
Maximum power consumption	25,2 kVA	40 kVA
Maximum voltage/current	400 V / 63 A	400 V / 100 A
Frequency	50 Hz	50 Hz
Other voltages on request	480 V - 575 V	480 V - 575 V
Other frequencies on request	60 Hz	60 Hz
CONTROL		
Temperature adjustment	+40°C à +240°C (+400°C opt.)	+40°C à +240°C (+400°C opt.)
Heating time adjustment Maximum temperature ∆ Temperature	0-99 hours +240°C 20-50°C	0-99 hours +240°C 20-50°C
Temperature probe Reference: Tool +	2 TEMP PROBE 1000	2 TEMP PROBE 1500°
Heating modes - Time - Ramp - Temp. with 1 sensor - Temp. with 2 sensors	•	•
Temperature control precision	+/-2°C	+/-2°C
Temperature holding at the end of cycle	•	•
Demagnetising	Automatic	Automatic
Residual magnetism	< 2 A / cm	< 2 A / cm
Audible signal	•	•
APPLIANCE DESIGN		
Dimensions (L x W x H) (mm)	1080 x 500 x 1350	1500 x 800 x 1600
Space between pivots A and B (1)	435 x 495 mm	685 x 705 mm
Weight (without yoke)	280 kg	650 kg
Pivoting arm	no	no
Trolley (optional)	•	•
PARTS TO BE HEATED		
Maximum weight	800 kg	1600 kg
Minimum bore diameter with smallest yoke.	40 mm	85 mm
Maximum external diameter	1500 mm	2000 mm
Maximum width	485 mm	695 mm

 $^{^{\}star}$ length of probe wire (e.g. 400: 400 = 400 mm)







YOKES AND OPTIONAL E	QUIPMENT					> P 14/16
TECHNICAL DATA	SmartTEMP S	SmartTEMP M	SmartTEMP L	SmartTEMP XL / XL Pivot	SmartTEMP XXL	SmartTEMP XXXL
DIMENSIONS (mm) STANDAR	D YOKES (•) AND OP	TIONAL (°)			Pivotin	yoke
Bore diameter of part to be heated		References: TOOL	ST/ (Size of the devi	ce) YOKE (Bore diameter capac	city), e.g. TOOL ST/S YOKE 10	1
10 mm	○ ST/S YOKE 10 7x7x200	• ST/M YOKE 10 7x7x280				
15 mm	ST/S YOKE 15 10x10x200	○ ST/M YOKE 15 10x10x280				
20 mm	• ST/S YOKE 20 14x14x200	ST/M YOKE 20 14x14x280	ST/L YOKE 20 14x14x350			
30 mm			• ST/L YOKE 30 20x20x350	○ ST/XL (/XL-P) YOKE 30 20x20x490		
35 mm	• ST/S Y0KE 35 25x24x200	• ST/M YOKE 35 25x24x280				
40 mm						
45 mm	○ ST/S Y0KE 45 30x26x200	○ ST/M YOKE 45 30x26x280	• ST/L YOKE 45 30x26x350	o ST/XL (/XL-P) YOKE 45 30x26x490	○ ST/XXL Y0KE 45 30x26x750	
60 mm	• ST/S Y0KE 60 40x38x200	○ ST/M YOKE 60 40x38x280	• ST/L YOKE 60 40x38x350	• ST/XL (/XL-P) YOKE 60 40x38x490	○ ST/XXL Y0KE 60 40x38x750	
70 mm		• ST/M YOKE 70 50x48x280	ST/L YOKE 7050x48x350	○ ST/XL (/XL-P) YOKE 70 50x48x490	○ ST/XXL YOKE 70 50x48x750	
85 mm			○ ST/L YOKE 85 60x60x350	○ ST/XL (/XL-P) YOKE 85 60x60x490	○ ST/XXL YOKE 85 60x60x750	OST/XXXL YOKE 85 60x60x1080
100 mm			• ST/L YOKE 100 70x70x350	○ ST/XL (/XL-P) YOKE 100 70x70x490	○ ST/XXL YOKE 100 70x70x750	
115 mm				• ST/XL (/XL-P) YOKE 115 80x80x490	 ST/XXL YOKE 115 80x80x750 	ST/XXXL YOKE 11: 80x80x1080
130 mm					o ST/XXL YOKE 130 90x90x750	
145 mm					• ST/XXL YOKE 145 100x100x750	O ST/XXXL YOKE 145 100x100x1080
215 mm						• ST/XXXL Y0KE 21: 150x150x1080
OPTIONAL EXTENSION YOKES						
Dimensions (L x I x h) (mm)	References :	TOOL ST/ (Size of the	device) EXTENSION Y	OKE (extension height)		
40 x 50 x 75	ST/S EXTENSION YOKE 75					
50 x 62 x 120		ST/M EXTENSION YOKE 120				
70 x 82 x 150			ST/L EXTENSION YOKE 150			
80 x 80 x 150				ST/XL-P EXTENSION YOKE 150		
80 x 80 x 200				ST/XL-P EXTENSION YOKE 200		
OPTIONAL EQUIPMENT						
Carrying case	ST/S CARRYING CASE					
Trolley				ST/XL (/XL-P) TROLLEY	ST/XXL TROLLEY	
Lifting device					ST/XXL LIFTING DEVICE	ST/XXXL LIFTING DEVICE






	> P 18
TOOL BP SET (size) / Bore Puller	
BP Set 5-44 7 clamps 1 against adjustable support 1 slide hammer	BP Set 45-100 3 clamps 1 against adjustable support
5 to 44	45 to 100
405 x 345 x 100	490 x 500 x 130
5	12
50 kN	50 kN
	BP Set 5-44 7 clamps 1 against adjustable support 1 slide hammer 5 to 44 405 x 345 x 100

➤ Description of components of the BP case Set 5-44

Bulley	For bearing	g with bore	Thread	Length	Moight (g)	
Puller	Min.	Max.	Thread	(L - mm)	Weight (g)	
BP 5-7	5	7	M8	27	60	
BP 8-11	8	11	M8	40	40	
BP 12-15	12	15	M8	53	120	
BP 16-19	16	19	M8	53	140	
BP 20-26	20	26	M8	55	260	
BP 28-34	28	34	M8	60	320	
BP 35-44	35	44	M8	78	410	

➤ Description of components of the BP case Set 45-100

Puller	For bearing	g with bore	Throad	Length	Weight (g)
ruller	Min.		Thread	(L - mm)	Weight (g)
BP 45-58	45	58	M10	91	860
BP 56-75	56	75	M10	115	2040
BP 74-100	74	100	M10	125	3140











DEEP-GROOVE BALL BEARING F	PULLER KIT > F	P 19				
Reference	TOOL BBPS 10-100 / Ball bearing puller set					
Contents	3 shafts, 28 arms, 22 metal rings, 3 o-rings, 1 crank, 1 centering pad					
Bore diameter	For bearing extraction from 10 to 100 mm					
Case dimensions	490 x 500 x 130 mm					
Case weight	8.4 kg					
Capacity	70 kN (7 tons)					


Puller	For bearing	y with bore		Weight		
i unci	Min.	Max.	A	С	L	(g)
BBPSA	10	25	A1/A2 - 140 A3 - 160	5 6	A1/A2 - 160 A3 - 180	260 – 420
BBPSB	20	60	170	8	196	550 - 820
BBPSC	17	100	200	10	237	1260 – 1800





^{*} Bearing not requiring an extraction ring.
(1) - Our recommendations may change depending on the make of the bearing.












SELF-CENTERING PULLER (combined with 2/3 arms) > P										
Reference	Reference TOOL SCMP 2/3-(Max. reach) / Self-Center Mech Puller									
	Capacity	Max. reach	Spi	Jaws dimensions			Weight			
Туре	(tons) (mm)	Min. (mm)	Max. (mm)	A (mm)	B (mm)	C (mm)	(kg)			
SCMP 2/3-120	2	80	36	120	8	6	15	1.6		
SCMP 2/3-180	3	120	38	180	6	7	15	2.3		
SCMP 2/3-270	5	160	42	270	11	10	25	4.3		






SELF-CENTER	SELF-CENTERING HYDRAULIC PULLER (combined with 2 or 3 arms) > F											P 21
Reference	TOOL SCHP (C	TOOL SCHP (Capacity) TONS / Self-Center Hyd Puller										
Tuno	Capacity Max. reach		Cylinder stroke H			Dimensions (mm)					Weight	
Туре	(ton) (mm)	(mm)	(mm)	Min.	Max.	А	В	С	Е	F	G	(kg)
SCHP 4 Tons	4	190	60	68	315	13	10	22	40	42	22	9
SCHP 12 Tons	12	300	85	90	515	15	16.5	29	70	60	28	17
SCHP 20 Tons	20	325	111	120	520	20	27	33	62	80	40	28
SCHP 30 Tons	30	415	111	120	620	20	27	38	85	98	50	39
















ACCESSORY CASE FO	ACCESSORY CASE FOR HYDRAULIC PULLER										
Reference	TOOL AS-SCHP (Hydraulic	OL AS-SCHP (Hydraulic extractor capacity) T / acc set hyd puller									
Contents	1 pulling arm, 2 braces, 1 se	1 pulling arm, 2 braces, 1 separator, 2 blades with 2 threaded studs									
Reference	Max. reach (mm)										
AS-SCHP 4 T	250	15 - 110	7	of the same							
AS-SCHP 12 T	380	45 - 290	22								

TRI-SEC	TION PULLING	PLATE				;	► P 23						
Reference	:	TOOL BP3S 5	0-210 / TRI-SECTION PULLIN	IG PLATE									
Materials	Materials Forged steel alloy												
DIMENSIONS (mm)													
	Shaft diameter Min. (A1) / Max. (A2) (mm)		Capacity Max spread B (ton) (mm)		Thread E	Thickness F (mm)	Weight (kg)						
26	160	4	216	240	5/8" – 11 UNC	8	3.5						
50	210	8	280	285	3/4" - 16 UNF	31	5.5						
90	340	12	460	430	7/8" – 16 UNF	45	16.5						
140	495	30	660	600	1" – 14 UNF	61	41						














PULLER - STRIPPING KIT	> P 24
Reference	TOOL BPES 10-105
Contents	1 adjustable bridge, 1 separator, 2 removable puller arms 2 extensions, 1 tip protector, 2 coupling nuts
Case dimensions	490 x 500 x 130 mm
Case weight	11 kg
Capacity	100 kN (10 tons)

➤ Description of components of the BPES case 10-105

	Shaft diameter (mm)	Bore diameter (mm)	Outside diameter (mm)	Max. reach (mm)
Separator	10-105	-	175 (max.)	150
Internal gripping puller	-	159-222	-	160
External gripping puller	-	-	30-155	160










Min. 10 - Max. 105 Reach max. : 150mm

HYDRAULIC PULLER F	FOR MOUNT	ING AND RE	MOVAL			HYDRAULIC PULLER FOR MOUNTING AND REMOVAL > P 25											
Reference		TOOL PUSH	/PULLER 8/	12 Tons													
Contents		1 double acting hydraulic cylinder, 3 arms, 3 extensions, 1 internal gripping puller															
	Capacity	Reach	Spread - A Dimensions					ns		Weight							
Туре	(ton)	(max.)	Min.	Max.	В	С	D	Е	F	(kg)							
Thrust	8	130	44	280	270	140	28	M12-P1.75	30								
Extraction (external)	12	240*	85	300	260	140	28	-	-	19.5							
Extraction (internal)	8	105	110	210	130-150	_	-	1"-12UNF	-								

^{*} without adapter (180 mm with adapter)















HYDRAULIC NUTS (equipped with automatic piston return dev	ice)	➤ P 28
References	TOOL HMV (size) EBF / Hydraulic Nut (metric) TOOL HMVC (size) EBF / Hydraulic Nut (inches)	
Materials		
HMV 10 EBF – HMV 40 EBF	Fine metric thread according to ISO 965-1998 Class 6H tolerance	
HMV 41 EBF – HMV 200 EBF	Trapezoidal thread according to ISO 2901-1993 Class 7H tolerance	
Nuts Sizes ≤ HMV 54 EBF Sizes ≤ HMV 92 EBF Sizes ≤ HMV 200 EBF	Recommended pump references: Pump 700b-0.3 I / Pump 700b-0.9 I Pump 700b-0.9 I Contact us	
Component Reference - hydraulic nuts		
Set of O-rings	Nut Reference followed by / Piston Seals: Example: TOOL HMV 15 / Piston Seals	
Ball valve	1500 bar Reference: TOOL HMV BALL PLUG 1/4	
Quick coupling connection (male)	With seal washer and connecting nipple Reference : TOOL HMV NIPPLE 1/4 Dimensions: see page 50	

A-A (1:2)







DIMENSION	S (MM) AND V	WEIGHT (KG) (F HYDRAUL	IC NUTS (met	ric)					
Size	Thread	Outside diameter (mm)	Total width (mm)	Piston diameter (mm)	Permissible stroke of the piston (mm)	Flange width (mm)	Body width (mm)	Diameter (mm)	Surface of the piston (mm²)	Weight (kg)
HMV EBF	G	D	В	max. d2		B1	B2	d1		
10	M50x1,5	114	43	110	5	5	38	50.5	2850	2.9
11	M55x2	120	43	116	5	5	38	55.5	3050	3
12	M60x2	125	43	121	5	5	38	60.5	3250	3
13	M65x2	130	43	126	5	5	38	65.5	3500	3.2
14	M70x2	135	43	131	5	5	38	70.5	3650	3.4
15	M75x2	140	43	136	5	5	38	75.5	3850	3.6
16	M80x2	146	43	142	5	5	38	80.5	4150	3.9
17	M85x2	150	43	146	5	5	38	85.5	4300	4
18	M90x2	156	43	152	5	5	38	90.5	4850	4.2
19	M95x2	162	43	158	5	5	38	95.5	5050	4.5
20	M100x2	166	44	162	5	6	38	100.5	5100	4.6
21	M105x2	172	44	168	5	6	38	105.5	5200	4.9
22	M110x2	178	44	174	5	6	38	110.5	5400	5.2
23	M115x2	182	44	178	5	6	38	115.5	5800	5.2
24	M120x2	188	44	184	5	6	38	120.5	5950	5.5
25	M125x2	192	44	188	5	6	38	125.5	6350	5.6
26	M130x2	198	44	194	5	6	38	130.5	6450	5.9
27	M135x2	204	44	200	5	6	38	135.5	6900	6.1
28	M140x2	208	45	204	5	7	38	140.5	7250	6.2
29	M145x2	214	46	210	5	7	39	145.5	7400	6.7
30	M150x2	220	46	216	5	7	39	150.5	7600	6.8
31	M155x3	226	46	222	5	7	39	155.5	8450	7.2
32	M160x3	232	47	228	6	7	40	160.5	8650	7.8
33	M165x3	238	47	234	6	7	40	165.5	8750	8.1
34	M170x3	244	48	240	6	7	41	170.5	9800	8.6
36	M180x3	256	48	252	6	7	41	180.5	11250	9.4
38	M190x3	270	50	266	7	8	42	191	11800	10.7
40	M200x3	282	51	278	8	8	43	201	12100	11.7
41	Tr205x4	288	51	284	8	8	43	207	13050	12.2
42	Tr210x4	294	52	290	9	8	44	212	13400	12.7
43	Tr215x4	300	52	296	9	8	44	217	14050	13.2
44	Tr220x4	306	52	302	9	8	44	222	14800	13.7
45	Tr225x4	312	53	308	9	8	45	227	15150	14.7
46	Tr230x4	318	53	314	9	8	45	232	15450	14.7
47	Tr235x4	326	54	322	10	8	46	237	16600	16.2
48	Tr240x4	330	55	326	10	9	46	242	17250	16.2
50	Tr250x4	342	55	338	10	9	46	252	17550	17.7
52	Tr260x4	356	56	352	11	9	47	262	19150	19.2
54	Tr270x4	368	57	364	12	9	48	272	20350	20.7
56	Tr280x4	380	58	376	12	9	49	282	21050	22.2
58	Tr290x4	390	58	386	13	9	49	292	22350	22.7
60	Tr300x4	404	61	400	14	10	51	302	23600	25.7







DIMENSION	S (MM) AND \	WEIGHT (KG) (OF HYDRAUL	IC NUTS (met	ric)					
Size	Thread	Outside diameter (mm)	Total width (mm)	Piston diameter (mm)	Permissible stroke of the piston (mm)	Flange width (mm)	Body width (mm)	Diameter (mm)	Surface of the piston (mm²)	Weight (kg)
HMV EBF	G	D	В	max. d2		B1	B2	d1		
62	Tr310x5	416	62	412	14	10	52	312	24850	27,2
64	Tr320x5	428	63	424	14	10	53	322	26250	29,7
66	Tr330x5	438	63	434	14	10	53	332	27500	30,2
68	Tr340x5	450	64	446	14	10	54	342	27750	31,7
69	Tr345x5	456	64	452	14	10	54	347	29350	32,7
70	Tr350x5	464	66	460	14	10	56	352	29800	35,2
72	Tr360x5	472	66	468	15	10	56	362	31250	35,7
73	Tr365x5	482	68	478	15	11	57	367	31600	38,7
74	Tr370x5	486	68	482	16	11	57	372	33300	39,2
76	Tr380x5	498	69	494	16	11	58	382	33500	40,7
77	Tr385x5	504	69	500	16	11	58	387	34050	41,2
80	Tr400x5	522	71	518	17	11	60	402	36600	45,7
82	Tr410x5	534	72	530	17	11	61	412	38200	48,2
84	Tr420x5	546	72	542	17	11	61	422	39900	50,2
86	Tr430x5	556	73	552	17	11	62	432	40750	52,7
88	Tr440x5	566	74	562	17	12	62	442	42400	54,2
90	Tr450x5	580	76	576	17	12	64	452	44100	57,7
92	Tr460x5	590	76	586	17	12	64	462	45100	60,2
94	Tr470x5	602	77	598	18	12	65	472	46800	62,2
96	Tr480x5	612	77	608	19	12	65	482	48600	63,2
98	Tr490x5	624	78	620	19	12	66	492	49500	66,2
100	Tr500x5	636	79	630	19	12	67	502	49950	70,2
102	Tr510x6	648	80	642	20	12	68	512	53300	74,2
104	Tr520x6	658	81	652	20	13	68	522	54250	75,2
106	Tr530x6	670	82	664	21	13	69	532	56150	79,2
108	Tr540x6	682	82	676	21	13	69	542	58200	81,2
110	Tr550x6	693	83	687	21	13	70	552	59150	84,2
112	Tr560x6	704	84	698	22	13	71	562	61150	88,2
114	Tr570x6	716	85	710	23	13	72	572	63200	91,2
116	Tr580x6	726	85	720	23	13	72	582	64200	94,2
120	Tr600x6	748	86	742	23	13	73	602	67400	100,2
126	Tr630x6	782	88	776	23	14	74	632	72850	110,2
130	Tr650x6	804	89	798	23	14	75	652	76100	115,2
134	Tr670x6	826	90	820	24	14	76	672	79450	120,2
138	Tr690x6	848	91	842	25	14	77	692	84200	127,2
142	Tr710x7	870	93	864	25	15	78	712	87700	135,2
150	Tr750x7	912	94	906	25	15	79	752	95050	146,2
160	Tr800x7	965	96	959	25	16	80	802	103800	161,2
170	Tr850x7	1020	99	1014	26	16	83	852	114450	181,2
180	Tr900x7	1075	103	1069	30	17	86	902	123950	205,2
190	Tr950x8	1126	103	1120	30	17	86	952	135450	218,2
200	Tr1000x8	1180	105	1174	34	17	88	1002	145700	239,2



DIMENSION	(MM) AND V	WEIGHT (KG)	OF HYDRAU	LIC NUTS (di	mension in i	nches)					
Size	Thread	Number of threads per inch	Outside diameter (in.)	Piston diameter (in.)	Piston diameter (in.)	Permissible stroke of the piston (in.)	Flange width (in.)	Body width (in.)	Diameter (in.)	Surface of the piston (in.²)	Weight (lb)
HMVC EBF	G		D	В	max. d2	\/	B1	B2	d1		
10	1,967	18	4,5	1,7	4,4	0,20	0,20	1,5	2,0	4,4	6,3
11	2,157	18	4,7	1,7	4,6	0,20	0,20	1,5	2,2	4,8	6,8
12	2,360	18	4,9	1,7	4,8	0,20	0,20	1,5	2,4	5,1	7,2
13	2,548	18	5,1	1,7	5,0	0,20	0,20	1,5	2,6	5,4	7,6
14	2,751	18	5,3	1,7	5,2	0,20	0,20	1,5	2,8	5,8	7,9
15	2,933	12	5,5	1,7	5,4	0,20	0,20	1,5	3,0	6,1	8,3
16	3,137	12	5,7	1,7	5,6	0,20	0,20	1,5	3,2	6,4	8,7
17	3,340	12	5,9	1,7	5,8	0,20	0,20	1,5	3,4	6,7	9,1
18	3,527	12	6,1	1,7	6,0	0,20	0,20	1,5	3,6	6,8	9,5
19	3,730	12	6,4	1,7	6,2	0,20	0,20	1,5	3,8	7,5	10,0
20	3,918	12	6,5	1,7	6,4	0,20	0,24	1,5	4,0	7,5	10,4
21	4,122	12	6,8	1,7	6,6	0,20	0,24	1,5	4,2	8,1	11,0
22	4,325	12	7,0	1,7	6,9	0,20	0,24	1,5	4,4	8,8	11,6
24	4,716	12	7,4	1,7	7,2	0,20	0,24	1,5	4,8	9,4	12,4
26 28	5,106 5,497	12 12	7,8 8,2	1,7	7,6	0,20 0,20	0,24	1,5	5,2 5,6	10,1 10,7	13,2
30	5,888	12	8,7	1,8 1,8	8,0 8,5	0,20	0,28 0,28	1,5 1,5	6,0	12,3	14,3 16,0
32	6,284	8	9,1	1,9	9,0	0,24	0,28	1,6	6,4	14,0	18,0
34	6,659	8	9,6	1,9	9,4	0,24	0,28	1,6	6,8	15,8	19,9
36	7,066	8	10,1	1,9	9,9	0,24	0,28	1,6	7,2	17,7	21,5
38	7,472	8	10,6	2,0	10,5	0,24	0,20	1,7	7,6	18,5	24,9
40	7,847	8	11,1	2,0	10,9	0,20	0,31	1,7	8,0	19,4	27,3
44	8,628	8	12,0	2,0	11,9	0,31	0,31	1,7	8,8	21,1	31,9
46	9,125	8	12,5	2,1	12,4	0,31	0,31	1,8	9,2	21,9	34,7
48	9,442	6	13,0	2,2	12,8	0,35	0,35	1,8	9,6	25,4	37,8
52	10,192	6	14,0	2,2	13,9	0,35	0,35	1,9	10,4	27,2	44,4
56	11,004	6	15,0	2,3	14,8	0,39	0,35	1,9	11,2	30,7	51,4
60	11,785	6	16,1	2,4	16,0	0,39	0,39	2,0	12,0	37,0	64,4
64	12,562	6	16,9	2,5	16,8	0,43	0,39	2,1	12,8	39,2	70,8
68	13,339	5	17,7	2,5	17,6	0,47	0,39	2,1	13,5	41,4	75,7
72	14,170	5	18,9	2,6	18,7	0,51	0,39	2,2	14,3	51,8	89,7
76	14,957	5	19,7	2,7	19,5	0,55	0,43	2,3	15,1	54,4	98,2
80	15,745	5	20,9	2,8	20,7	0,55	0,43	2,4	15,9	54,8	116,4
84	16,532	5	21,9	2,8	21,7	0,55	0,43	2,4	16,7	60,8	127,7
88	17,319	5	22,6	2,9	22,5	0,55	0,43	2,4	17,5	63,4	134,1
92	18,107	5	23,6	3,0	23,5	0,59	0,47	2,5	18,3	71,3	150,6
96	18,894	5	24,4	3,0	24,3	0,63	0,47	2,6	19,1	78,2	158,0
100	19,682	5	25,6	3,1	25,4	0,63	0,47	2,6	19,8	85,7	181,6
106	20,867	4	26,8	3,2	26,6	0,67	0,51	2,7	21,0	85,89	199,4
112	22,048	4	28,1	3,3	28,0	0,71	0,51	2,8	22,2	87,0	221,1
120	23,623	4	29,9	3,4	29,8	0,75	0,51	2,9	23,8	101,0	249,2
126	24,804	4	31,1	3,5	30,9	0,75	0,55	2,9	25,0	105,6	266,4
134	26,379	4	33,1	3,5	32,9	0,87	0,55	3,0	26,5	125,3	307,8
142	27,961	3	34,6	3,7	34,5	0,91	0,59	3,1	28,1	132,1	337,1
150	29,536	3	36,2	3,7	36,1	0,91	0,59	3,1	29,7	138,9	358,1
160	31,504	3	38,2	3,8	38,0	0,98	0,63	3,1	31,7	147,4	387,1
170	33,473	3	40,6	3,9	40,4	1,02	0,63	3,3	33,6	179,2	448,0
180	35,441	3	43,3	4,1	43,1	1,10	0,67	3,4	35,6	238,6	545,6 575.2
190	37,410	3	45,3	4,1	45,1	1,10	0,67	3,4	37,6	250,8	575,3







MANUAL HYDRAULIC PUMP KITS		> P 29							
References	TOOL PUMP SET 700B-(Reservoir capacity)	TOOL PUMP SET 700B-(Reservoir capacity) L / Pump with accessories							
Contents	Pump Set 700b-0.3 L	Pump Set 700b-0.9 L							
(A) 1 2-stage manual pump	700 bar pump with 0.3 litre reservoir	700 bar pump with 0.9 litre reservoir							
B 1 adaptor for pressure gauge*	1/4" male, 3/8" female	3/8" male, 3/8" female							
© 1 pressure gauge	700 bar	700 bar							
① 1 hose	700 bar, length 1.5 m	700 bar, length 3 m							
E 1 quick coupling connection (female)	G ¼ (1500 bar)	G ¼ (1500 bar)							
➤ Description of the manual hydraulic p	ump kit components								

(A) ULTRA LI	GHT MANUAL PUMP ((with two stages)					≻ P 29		
Reference				TOOL PUMP 700b - (reservoir capacity) L					
Material				Glass fib	re reinforced composite	e tank			
Reference TOOL +	Nominal pressure 1 st stage (bar)	Nominal pressure 2 nd stage (bar)	Volume 1 st s (cr	tage	Volume/stroke 2 nd stage (cm³)	Tank capacity (cm³)	Weight (bare pump) (kg)		
PUMP 700b-0.3I	13	700	3.	6	0.9	320	2.4		
PUMP 700b-0.9l	13	700	11	1.3 2.5		900	4.1		

Reference		DIMENSIONS (mm)												
T00L +	А	В	С	D	Е	G	Н	J	L	M	N	Р	S	
PUMP 700b-0.3l	185	336	28	85	28	1/4" - 18 NPTF	319	19	143	-	95	80	7	
PUMP 700b-0.9l	344	533	36	99	33	3/8" - 18 NPTF	522	30	177	16	120	-	-	








® PRESSURE GAUGE ADAPTOR ACCORDING	G ТО РИМР		≻ P 29
Reference	TOOL gauge adapter (Reservoi	capacity) L	
Reference TOOL+	Pressure gauge port	Male end	Female end
GAUGE ADAPTER 0.3 I	NPTF	NPTF 1/4"	NPTF
GAUGE ADAPTER 0.9 I	1/4"	NPTF 3/8"	3/8"

© PRESSURE GAUGE		> P 29
Reference	TOOL PUMP GAUGE 700	
Permitted pressure	700 bar (10 000 psi)	Α Β
Precision (% full scale)	+/- 1.0 (-1.5%)	
Graduation	Bar	
Scales	Bar	
Large graduations	100	
Small graduations	20	
Connecting thread C	1/4" NPTF	
Diameter A	100 mm	
Height D	130 mm	С
Thickness B	35 mm	

(D) HIGH PRESSURE HOSE					>	P 29
Reference	TOOL HYDRAUL	IC HOSE (length in	n mm)			
Material	Thermoplastic re Polyurethane en	einforced with layer velope	rs of woven steel w	vire		
References	Max. working pressure (bar)	Inner diameter (mm)	Length (mm)	Weight (kg)	Connection end 1	Connection end 2 (male)
TOOL HYDRAULIC HOSE 1500	700	6.4	1,500	0.8	3/8" - 18 NPTF	G ¼ 750 bar
TOOL HYDRAULIC HOSE 3000	700	6.4	3,000	1.5	3/8" - 18 NPTF	G ¼ 750 bar

© QUICK COUPLING CONNECTION, FEMALE	(connection on end 2) > P 29
Reference	TOOL PUMP COUPLING 1/4
Material	High strength steel. Black zinc treatment
Type of valve	Flat face for minimum discharge of fluid on disconnection
Maximum service pressure	1500 bar



 $\label{eq:Note-Seal} \textbf{Note} - \text{Seal washer and connecting nipple included in HMV NIPPLE 1/4} \\ \text{are not represented on the drawing.}$

Thread A BSPP	d1 (mm)	d3 (mm)	Nut Hex1 (mm)	LF (mm)	d2 (mm)	Nut Hex2 (mm)	LM (mm)	LT (mm)	Ø (mm)	Reference Female TOOL+	Weight (g)	Reference Male TOOL+	Weight (g)
G 1/4	28.2	26.8	24	59.5	24.5	22	38	79.5	14.9	PUMP COUPLING 1/4	192	HMV NIPPLE 1/4	69





HEAT-RESISTANT GLOVES	> P 32
Reference	TOOL GLOVE HEAT RESISTANT
Material	KEVLAR
Lined	Coton
Single size	10.5
Maximum temperature	350°C
Quantity per packet	1

SET OF CALIBRATED FEELER GAI	UGES OF CALIBRATED	THICKNESS			> P 32
Reference	FEELER GAUGE TOOL	. (gauge length)			
	Number of gauges	Field of measurement (mm)	Blade thickness (1/100 of mm)	Length (mm)	Weight (g)
TOOL FEELER GAUGES 100			0.02 0.15 0.03 0.20 0.04 0.25	100	65
TOOL FEELER GAUGES 150	17	0.02 – 0.5	0.05 0.30 0.06 0.35 0.07 0.40	150	85
TOOL FEELER GAUGES 300			0.08 0.45 0.09 0.50 0.10	300	175





INFRARED THERMOMETER WITH LASER	> P 33
Reference	TOOL LASERTEMP 301 / IR Thermometer
APPLIANCE CHARACTERISTICS	
Spectral response	8 -14 mm
Optics	D.S : 30:1 (50 mm to 1500 mm)
Response time	Less than one second
Temperature range	From -50 to +850°C
Accuracy*	From -50 to -20°C: \pm 5°C From -20 to +200°C: \pm 1.5% of the reading \pm 2°C From +200 to +538 °C: \pm 2% of the reading \pm 2°C From +538 to +850°C: \pm 3.5% of the reading \pm 5°C
Display resolution	0.1°C
Emissivity	Adjustable between 0.10 and 1.00 (pre-set at 0.95)
Screen indication :	Indication of level exceeded "-01" for under-range "01" for over-range
Laser aiming device	Wave length : 630-670 nm output lower than 1mW, class 2 (II)
Indication of positive or negative temperature	Automatic (no indication for a positive temperature) Sign (-) for a negative temperature
Screen	4½ digits with backlit LCD screen
Auto switch-off:	After 7 seconds of inactivity High/low alarm
Thresholds	Flashing signal on screen and audible signal with adjustable thresholds
Supply	9 V alkaline battery
Battery life	38 hr (laser and backlight inactive) 15 hr (laser and backlight active)
Temperature for use	From 0 to +50°C
Storage temperature	From -20°C to +60°C
Relative humidity	From 10% to 90% RH in operation and less than 80% RH in storage
Dimensions	175 x 110 x 45 mm
Weight	230 g (including battery)
Memory	20 temperature values with unit of measurement (°C or °F)
* Accurate for an ambient temperature between 18 and 28°C (with relative humid	lity below 80%)
CHARACTERISTICS OF THE THERMOCOUPLE PROBE K	
Temperature range	From -40 to +400°C
Display range	From -50 to +1370°C
Resolution	0.1°C
Accuracy	±1.5% of the reading ±3°C
Cable length	1 m
The devices meet the following standards 1992, electromagnetic emissions EN 50081-1: 1992, electromagnetic interference EN 50082-1: 1992, electromagnetic susceptibility	





GLOSSARY

Descriptions	References	Catalogue pages	Technical data pages
Cold mounting case	TOOL IFT SET 33 / Industry Fitting Tool Set	P 09	P 36
"Contact corrosion" anti-fretting paste	LUB MOUNTING PASTE (packaging)	P 11	P 36
Articulated manual pin spanner	TOOL PS (min. size – max. size) / Pin Spanner	P 11	P 36
Articulated manual hook spanner	TOOL HS (min. size – max. size) /Hook Spanner	P 11	P 36
Induction heater	TOOL SmartTEMP (size) / Induction Heater	P 14-16	P 38
Only bar for induction heater	TOOL ST/ (Size of the device) – YOKE (Bore diameter capacity)	P 14-16	P 40
Temperature probe for induction heater	TOOL TEMP PROBE (size)	P 14-16	P 38-39
Bar lifting device for heater	TOOL ST/ (capacity) LIFTING DEVICE	P 16	P 39
Bore puller kit with internal gripping	TOOL BP SET (min. size - max. size)/ Bore Puller	P 18	P 41
Deep-groove ball bearing puller kit	TOOL BBPS 10-100/ball bearing / Puller set	P 19	P 42
Self-centering mechanical puller	TOOL SCMP 2/3 - (max. reach) / Self-Center Mech Puller	P 20	P 43
Self-centering hydraulic puller	TOOL SCHP (capacity) TONS /Self-Center Hyd Puller	P 21	P 43
Accessories case for self-centering hydraulic puller	TOOL AS-SCHP (capacity) T / Acc. Set Hyd Puller	P 22	P 44
Tri-section pulling plate	TOOL BP3S (shaft min. / max.) / Tri-Section Back Puller	P 23	P 44
Mechanical spindle puller-separator Kit	TOOL BPES 10-105 / Back Puller extract set	P 24	P 45
Hydraulic puller for mounting and removal	TOOL PUSH/PULLER 8/12 Tons	P 25	P 45
1/4" gas ball valve	TOOL HMV BALL PLUG 1/4	P 28	P 46
Set of O-rings for hydraulic nut	TOOL HMV (Size) / Piston Seals	P 28	P 46
Hydraulic nut with metric thread and piston return device	TOOL HMV (Size) EBF / Hydraulic Nut	P 28	P 46-49
Manual hydraulic pump kit	TOOL PUMP SET 700B (reservoir capacity) L / Pump with accessories	P 29	P 50
Oil for pump 700b	TOOL HYDRAULIC OIL 1L	P 29	P 50
Pump pressure gauge, 700 bars	TOOL PUMP GAUGE 700	P 29	P 51
Quick coupling connection, ¼ gas (female)	TOOL PUMP COUPLING 1/4	P 29	P 51
Pressure gauge adapter depending on pump	TOOL GAUGE ADAPTOR (reservoir capacity)	P 29	P 51
High-pressure hose with quick coupling connector (female)	TOOL HYDRAULIC HOSE (length mm)	P 29	P 51
Quick coupling connection, ¼ gas (male)	TOOL HMV NIPPLE 1/4	P 29	P 51
Thermal insulation gloves	TOOL GLOVE HEAT RESISTANT	P 32	P 52
Set of feeler gauges	TOOL FEELER GAUGES (length)	P 32	P 52
Infrared thermometer with laser sighting targeting ratio 30 : 1	TOOL LASERTEMP 301 / IR Thermometer	P 33	P 53





With You



NOTES	







With our "field" experts, you boost the operational efficiency of

- By cutting your maintenance costs;
- By improving the quality of your work;
- By optimizing the service life of equipment.

The Bearing box proposes:

- Practical training
- Technical assistance
- Demonstration of maintenance product tools

|--|

This document is the exclusive property of NTN-SNR ROULEMENTS. Any total or partial reproduction hereof without the prior consent of NTN-SNR ROULEMENTS is strictly prohibited. Legal action may be brought against anyone breaching the terms of this paragraph.

NTI-SNR ROULEMENTS shall not be held liable for any errors or omissions that may have crept into this document despite the care taken in drafting it. Due to our policy of continuous research and development, we reserve the right to make changes without notice to all or part of the products and specifications mentioned in this document.

 $\ \, \bigcirc$ NTN-SNR ROULEMENTS, international copyright 2018.



